



## ➤ Technical data

### Hei-MIX Incubator 1000

Standard supply voltage	230 V/50 Hz or 115 V/60 Hz
Power consumption (W)	335
Device fuses	T 2,0 A (230 V) or T 4,0 A (115 V)
Heating capacity (W)	290
Protective class (IEC 61140)	1 ⊕
Protection class (IEC 60529)	IP 30
Sound pressure level (dB(A)) (based on IEC 61010)	< 45
Motor	shaded pole motor
Heating	finned pipe heater
Air circulation	cross current fan
Overheat protection	self-resetting
Operating mode	continuous
Temperature control	electronic
Temperature range 230 V (°C)	5* - 65
Temperature setting	digital
Temperature accuracy (°C)	± 2 up to 50 °C heating temperature ± 4 from 50 °C heating temperature
Dimensions (w x h x d) (mm)	170 x 140 x 375
Weight (kg)	5.2

<b>Hood, 2-parts (PETG)</b>	<b>flat</b>	<b>high</b>	<b>XL</b>
Dimensions (w x h x d) (mm)	570 x 163 x 390	570 x 267 x 390	570 x 428 x 390
Volume (dm <sup>3</sup> )	28	45	77

\* The lowest possible temperature will always be approx. 5 °C above ambient temperature.