

Reax 20 - for 4 bottles (1-16 rpm)

P/N: 036130400



The resilient one with a capacity of up to 4 bottles

The Reax 20 is an ideal shaker for processing and storing samples that tend to sediment. The fields of application range from environmental technology to paint processing and quality assurance in the materials industry.

The maximum permissible weight is 30 kg, so that samples with a high solid content can also be properly mixed. Since this device sets great forces in motion, it is equipped with an emergency stop switch for your safety.

This overhead shaker can be ordered with a capacity of [4](#), [8](#) or [12](#) bottles. Also suitable for mixing cylinders or wide-neck bottles.

Reax 20 - for 4 bottles (1-16 rpm) - Technical Data

Overheat protection	self-resetting
Permissible ambient conditions	5 - 31 °C at 80 % rel. humidity 32 - 40 °C decreasing linearly up to max. 50 % rel. humidity
Weight	23 kg
Protection class IEC 60529	IP 21
Timer	-
Rotation speed range	1 - 16 rpm
Power input	280 W
Dimensions (w/d/h)	490 x 520 x 465 mm
Max. Load	30 kg
Operating Mode	-
Rotation speed setting	electronic control
Orbit / Stroke	-
Platform size	-
Accessories included	Tension plate for cap dia. up to 77 mm
Angle	-
Motion	overhead