

PRODUCT SPECIFICATIONS

Main Specifications	
Item Code	1900042-01
Temperature Range (°C)	-25°C / -10 °C
Temperature Range (°F)	-77 / -50 °F
Max. Ambient Temperature (°C)	+32 °C
Capacity (L)	400
Capacity (Cu.FT)	14.13
Exterior Dimensions WxDxH (Mm)	608 X 698 X 1840
Exterior Dimensions WxDxH (Inches)	24 X 28 X 72
Interior Dimensions WxDxH (Mm)	500 X 540 X 1550
Interior Dimensions WxDxH (Inches)	20 X 21 X 61
Weight (KG)	70
Weight (Lb)	154
Insulation (Mm)	50
Insulation (Inches)	1.97
Cooling Technology	Static Cooling
Controller Model / Probe Type	Honker / NTC
Power Supply (V)	110
Frequency (Hz)	60
AMP (A)	1.9
Display / Data / Alarm	
Alarm Display As Text - Not Codes	No
Visual / Acoustic Alarm	Yes / Yes
Power Failure Alarm	Yes
Adjustable High/Low Temperature Alarm	Yes / Yes
Open Door Alarm	Yes
Probe Failure Alarm	Yes
Low Battery Alarm	Yes
Voltage Free Contact For Remote Alarm (E.G. GSM Alarm Module)	Yes
Electronic Data Logger	Yes
USB Port For Software Update & Data Download	Yes
Display Type	Digital
Number Of Optional Reference Probes	N/A
Other Features	
Access Port For External Probe Etc. (Int. Diameter Mm)	Yes (20)
Light	Yes
Lock With Key	Yes
Castors (Total Pcs) / Castors With Brake (Pcs)	4 / 2
Reversible Doors (Pcs)	Yes
Fixed Shelves (Pcs) / Adjustable Shelves (Pcs)	0 / 7
Max. No. Of Shelves (Pcs) / Recommended Max. No. Of Shelves (Pcs)	7 / 7
Max Load Per Shelf (Kg)	26
Refrigerant & Cabinet	
Number Of Compressors	1
Refrigerant	R290
Interior Cabinet Material	Powder Coated Aluminum Plate
Exterior Cabinet Material	Powder Coated Galvanized Steel
Colour (Exterior Cabinet)	White
Foam Agent	Cyclopentane
Shipping	
Shipping Weight (Kg)	84
Shipping Weight (Lb)	185
Shipping Dimensions WxDxH (Cm)	65 X 75 X 192.8
Shipping Dimensions WxDxH (Inches)	26 X 30 X 76
Shipping Volume (M ³)	0.94
Shipping Volume (Cu.FT)	33.2
Downloads	