



Boekel Rocker II™

FEATURES

- Ambient temperature range 4°C to 40°C
- Low voltage power is supplied by wall mount transformer
- Accepts a wide variety of flasks and plates and tubes
- Adjust tilt angle and speed without the need for tools
- Thin power cord easily passes through incubator door gaskets
- Supplied with flat non-skid mat
- Power pac is UL, CSA and CE approved
- Unit is CE marked

ACCESSORIES

Catalog No.	Description
260355	Stacking Tray (Supplied with rubber non-skid mat)
C2202208	Dimpled Mat

Catalog No.	Rocker II (115 VAC) 260350	Rocker II (230 VAC) 260350-2
Adjustable Speed	3 - 25 rpm	3 - 25 rpm
Tilt Angle	0° to 20°	0° to 20°
Load Limit	6 lbs. / 2.7 kgs.	6 lbs. / 2.7 kgs.
Operating Temperature	4°C to 40°C	4°C to 40°C
Stacking Tray Weight	1.5 lbs. / 0.7 kgs.	1.5 lbs. / 0.7 kgs.
Stacking Tray Clearance	2.5" (6.3 cm)	2.5" (6.3 cm)
Product Dimensions w/o platform W x D x H	7.5" x 7" x 5" (19.1 cm x 17.8 cm x 12.7 cm)	
Product Dimensions w/platform W x D x H	12" x 12" x 7" (30.5 cm x 30.5 cm x 17.8 cm)	
Power	12 V dc, 0.5 A via 115/ 230 V AC adapter CE marked	
Shipping Weight	13 lbs. / 5.9 kgs.	13 lbs. / 5.9 kgs.



282000

Boekel Tube Rockers

FEATURES

- Provides gentle rocking action for mixing of specimens
- Low profile and small footprint minimizes bench space
- Fixed tilt angle - 35°
- Supplied with non-slip autoclavable tube pad (silicon rubber)
- Power pac is CSA, CE and PSE approved



280150



260450

	Tube Rocker XL Variable Speed	Tube Rocker Mini Variable Speed	Tube Rocker Mini Fixed Speed
Catalog No.	282000	280150	260450
Speed	5 - 25 rpm	5 - 25 rpm	18 rpm
Tilt Angle	35° angle fixed		
Tube Capacity	Up to 19 tubes maximum 120 mm long	Up to 8 tubes maximum 120 mm long	
Load Capacity	2.8 lbs. / 1.3 kgs.	1.8 lbs. / 0.8 kgs.	
Product Dimensions W x D x H	16" x 4.7" x 5" (50 cm x 12 cm x 12.7 cm)	8.6" x 4.7" x 5" (21.8 cm x 12 cm x 12.7 cm)	
Power	12 VDC, 0.5 A via 100/240 Volt AC adapter		
Shipping Weight	8 lbs. / 3.6 kgs.	5 lbs. / 2.26 kgs.	