



Boekel Mini Tube Rotator

FEATURES

- A Variable Speed with LCD display
- Includes 260751 Carousel for 36 x 1.5/2.0ml tubes
- Provides complete 360° Rotation
- An adjustable 0-90° Mixing Angle
- Small footprint for your bench – we know you need all the space you can get!
- Interchangeable carousels for all common laboratory tubes
- Cold Room and Incubator compatible
- AC Adapter 115v to 240V with UL/CSA and CE markings

Mini Tube Rotator

| | |
|--------------------------------|--|
| Catalog No. | 260750 |
| Speed | Variable 4-18 RPMs |
| Mixing Angle | Adjustable 0-90° |
| Load Capacity | 1.75 lbs |
| Carousel Capacity | (36) 1.5/2.0 ml tubes, (10) 10/15 ml and (16) 5/7 ml tubes, (6) 50ml tubes |
| Operating Temperature | +4°C to 40°C |
| Product dimensions (W x D x H) | 9" x 5" x 6" (22.8 cm x 12.7 cm x 15.2 cm) |
| Power Requirements | 12v DC via 100-240 V AC Adapter |
| Shipping Weight | 4.5 lbs. / 2.0 kgs. |

ACCESSORIES

| Catalog No. | Interchangeable Platforms |
|-------------|---|
| 260751 | Carousel, 36 x 1.5/2.0 ml Tubes |
| 260752 | Carousel, 10 x 10/15ml Tubes and 16 x 5/7ml Tubes |
| 260753 | Carousel, 6 x 50 ml Tubes |

Boekel Tube Rotator

FEATURES

- Digital microprocessor control
- Adjustable speed provides gentle or vigorous mixing action
- Adjustable angled head offers mixing angles from 90 to 180 degrees
- Five carousel options provide greater versatility for the most tube mixing needs
- Includes 260653 - 14 Place Tube Carousel for 50mL
- Power pac is UL, CSA and CE approved
- Unit is CE marked

ACCESSORIES

| Catalog No. | Interchangeable Carousel |
|-------------|---|
| 260651 | 46 place tube carousel for 1.5/ 2.0 ml tubes |
| 260652 | 28 place tube carousel for 15 mL tubes |
| 260653 | 14 place tube carousel for 50 mL tubes |
| 260654 | 63 place tube carousel for 18.5 mm cul. tubes |
| 260655 | 63 place tube carousel for 14 mm cul. tubes |

Tube Rotator

| | |
|------------------------------|---|
| Catalog No. | 260650 |
| Speed | 4 - 80 rpm |
| Carousel angle | 90 - 180 degrees |
| Timer (with auto shut off) | Up to 99 hrs and 59 minutes |
| Carousel capacity | 46 x 9 - 11 mm tubes, 28 x 14 - 18 mm tubes, 14 x 27 - 34 mm tubes, 63 x 18.5 mm culture tubes (drum rotor) and 63 x 14 mm culture tubes (drum rotor) |
| Operating Temperature | +4°C to +40°C |
| Product Dimensions W x D x H | 12" x 17" x 15" (30.4 cm x 43.1 cm x 38.1 cm) |
| Power | 24.0 V DC, 2.70 A via 100 - 240 VAC adapter |
| Shipping Weight | 16 lbs. / 7.25 kgs. |

