

Product Specifications:

RPMS	Model # 280150 Model # 282000	5 – 25 RPM 5 – 25 RPM
Overall Dimensions	Model # 280150 Model # 282000	W: 8.6" D: 4.7" H: 5" W: 15.0" D: 5.0" H: 5"
Tilt Angle	Model # 280150 Model # 282000	Fixed at 35° Fixed at 35°
Tube Capacity	Model # 280150 Model # 282000	8 Tubes – max 120mm in length 18 Tubes – max 120mm in length
Load Capacity	Model # 280150 Model # 282000	Max 1.8 lbs Max 3.6 lbs
Power	Model # 280150 Model # 282000	12v dc, 0.5A via 100/240 V AC Adapter 12v dc, 0.5A via 100/240 V AC Adapter

Warranty:

When used in laboratory conditions and according to these operating instructions, Boekel warrants this product to be free of defective material and workmanship for a period of two years from the date of manufacture. The liability of Boekel for any defective equipment during the warranty period shall be limited to the repair of such equipment or replacement thereof without charge for parts or labor.

Service:

It is required to obtain a Returned Material Authorization (RMA) number before any Boekel products are returned for any reason. A Decontamination Certificate must be completed, signed by the user, and returned to Boekel Scientific prior to receiving the RMA number. Please consult the manufacturer or his agent if there is any doubt about the compatibility of decontamination or cleaning agents. Please be sure to mark the outside of the returned goods package with this RMA number to ensure prompt handling.

Boekel Scientific
855 Pennsylvania Boulevard
Feasterville, PA 19053
Phone: (215) 396-8200 or (800) 336-6929
Fax: (215) 396-8264
e-mail: boekel-info@boekelsci.com