



Boekel Jitterbug-2/Jitterbug-4 Microplate Thermoshaker

FEATURES

- Accommodates two or four standard microplates or strip trays
- Independently set temperature, shaking speed and mixing duration
- Chamber in a chamber design for excellent stability
- Smooth, quiet operation
- Temperature calibration
- Heated lid to provide greater uniformity
- Accommodates Std. 96, 384, and 536 Plates
- Power pac is UL, CSA and CE approved
- Unit is CE marked

	Jitterbug-2 - 2 Plate Capacity	Jitterbug-4 - 4 Plate Capacity
Catalog No.	270400	270440
Speed	250 to 1200 rpm	250 to 1200 rpm
Orbit	2 mm	2 mm
Stability	±0.1°C	±0.1°C
Uniformity	±0.2°C	±0.2°C
Timer (with auto shut off)	1 min to 96 hrs	1 min to 96 hrs
Time setting resolution	1 min	1 min
Temperature range	Ambient +5 to 60°C	Ambient +5 to 60°C
Product Dimensions W x D x H	10.5" x 10.6" x 6" (26.6 cm x 26.7 cm x 14.5 cm)	15.5" x 15.5" x 6" (38.5 cm x 27 cm x 14 cm)
Power	12 V DC, 4.5 A via 115/ 230 V AC adapter	12 V DC, 5.0 A via 115/ 230 V AC adapter
Shipping Weight	16 lbs. / 7.25 kgs.	16 lbs. / 7.25 kgs.


Boekel Microplate Shakers

FEATURES

- Compact with low profile and small footprint
- Reliable, regulated shaking for two or four microplates
- Simple screw attachments allow quick and easy fitting of any standard depth 96- or 384-well plates, holding the plates securely in place
- LCD Display
- Power pac is UL, CSA and CE approved
- Unit is CE marked

ACCESSORIES

Catalog No.	Interchangeable Platforms
270390	Platform for four microplates



	2 Plate Capacity	4 Plate Capacity
Catalog No.	270300	270340
Speed	250 to 1000 rpm	250 to 1000 rpm
Orbit	2 mm	2 mm
Timer (with auto shut off)	1 min to 96 hrs	1 min to 96 hrs
Time setting resolution	10 sec	10 sec
Product Dimensions W x D x H	7" x 7.25" x 3.5" (17.5 cm x 18.5 cm x 9 cm)	7" x 7.25" x 3.5" (17.5 cm x 18.5 cm x 9 cm)
Power	12 V dc, 0.5 A via 115/ 230 V AC adapter	12 V dc, 0.5 A via 115/ 230 V AC adapter
Shipping Weight	10 lbs. / 4.5 kgs.	10 lbs. / 4.5 kgs.