

## 5. Specifications

---

Electrical:	115 / 230V UL, CE and CSA approved
Temperature Range	Ambient + 5°C to 120°C With overtemp protection
Temperature Stability	+/- 0.2°C from 37°C to 100°C
Temperature Accuracy	+/- 0.25°C at 37°C
Control	Touch Screen with Alarms, Timers, and Temperature Step Control
Programs	Store up to 25 separate programs with 5 steps per each program & repeat function.
Capacities	1 Block, 2 Block and 4 Block Models
Optional Accessories	External Temperature Probe Aluminum Heating Blocks
Timer	Settable Up to 99 Hours, 59 Seconds or ∞
Operating Temperature	10°C to 30°
Product Dimensions: W x D x H	
1 Block	6" (153 mm) x 8.75" (223 mm) x 3.255" (83 mm)
2 Block	6" (153mm) x 12" (305mm) x 3.25" (83mm)
4 Block	6" (153 mm) x 18" (204mm) x 3.25" (83mm)
Product Weight / Shipping Weight	
1 Block	3.25 lbs / 1.5 kg
2 Block	4.9 lbs / 2.3 kg
4 Block	8.1 lbs / 3.7 kg