

Product Name:	NSWDR231SSG/0
Description:	<p>Corepoint Scientific™ White Diamond Series Laboratory and Medical Stainless Steel Refrigerator 23 Cu. Ft. Capacity</p> <p>One swing glass door, self-closing, right hinged, not reversible</p> <p>5 ea. Adjustable Shelves</p> <p>Microprocessor temperature controller</p> <p>Touch Screen Digital Temperature Display with user friendly interface</p> <p>Alarm Module with battery back-up to support temperature monitoring and alarms</p> <p>Password-protected control panel</p> <p>C°/F° switchable</p> <p>0.1° resolution</p> <p>Adjustable operating temperature: 1°C to 10°C (34°F to 50°F)</p> <p>Active temperature scale bar display</p> <p>Resettable 1-point min/max history</p> <p>Digital 24-hour temperature chart</p> <p>Temperature data logging</p> <p>USB port for data transfer and software updates</p> <p>Real-time operational display clock</p> <p>4-20mA output</p> <p>Adjustable alarm volume</p> <p>Audible and visual high/low temperature alarms</p> <p>2 probes; 1 in air and 1 in sample bottle</p> <p>Continuous product (simulated) temperature display</p> <p>Sensor error alarm</p> <p>Power failure alarm</p> <p>Door ajar alarm</p> <p>Low battery alarm</p> <p>Alarm validation (audible, visual, and remote alarm)</p> <p>Alarm mute with ring back</p> <p>Remote alarm contacts</p> <p>Customizable alarm time delay settings</p> <p>Forced draft air circulation</p> <p>Keyed door lock</p> <p>Magnetic door gaskets for positive seal</p> <p>Heavy duty door handle</p> <p>LED interior lights are safety shielded and switch controlled</p> <p>Probe access port (3/4")</p> <p>Stainless steel exterior</p> <p>White-powder coated aluminum interior with 304 stainless steel floor</p> <p>Easily cleaned smooth interior</p> <p>Hydrocarbon natural refrigerant (R290)</p> <p>Three year parts and labor warranty, plus an additional two year compressor parts warranty</p> <p>4 swivel casters (5 3/4")</p> <p>Exterior dimensions: 26 7/8" W x 34 3/4" D x 83 1/4" H with casters; 77 1/2" H without casters</p> <p>Cycle defrost</p> <p>115V, 60 Hz, 3 Amps, 1/5 HP</p> <p>ETL listed</p> <p>Shipping weight: 356 lbs.</p>