



designed for scientists



## EUROSTAR 60 control Package

/// Data Sheet

Package includes

EUROSTAR 60 control

R 2723 Telescopic stand

R 271 Boss head clamp

R 1345 Propeller stirrer, 4-bladed

RH 5 Strap clamp



designed for scientists

## Technical Data

Stirring quantity max. per stirring position (H2O) [l]	40
Motor rating input [W]	168
Motor rating output [W]	131
Motor principle	Brushless DC
Speed display	TFT
Speed range [rpm]	0/30 - 2000
Intermittent operation	yes
Viscosity max. [mPas]	50000
Output max. at stirring shaft [W]	126
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	60
Speed adjustment	stepless
Setting accuracy speed [rpm]	±1
Deviation of speed measurement n > 300rpm [%]	±1
Deviation of speed measurement n < 300rpm [rpm]	±3
Stirring element fastening	chuck
Connection for ext. temperature sensor	PT1000
Temperature display	yes
Chuck range diameter [mm]	0.5 - 10
Hollow shaft, inner diameter [mm]	11
Hollow shaft (push-through - when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	16
Extension arm length [mm]	220
Torque display	yes
Speed control	electronic
Nominal torque [Nm]	0.6
Torque measurement	trend
Deviation of torque measurement I [Ncm]	±6
Timer	yes
Timer display	TFT
Time setting range [min]	1 - 6000
Temperature measuring range [°C]	-10 - +350
Temperature measurement resolution [K]	0.1
Accuracy of temperature measurement [K]	±0.5 + tolerance PT1000 (DIN EN 60751 Class A)
Limit deviation temperature sensor [K]	≤ ± (0.15 + 0.002x T )
Housing material	alu-cast coating / thermoplastic polymer
Communication distance (depend on building) max. [m]	150
Dimensions (W x H x D) [mm]	86 x 267 x 230
Weight [kg]	4.7
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 40
RS 232 interface	yes
USB interface	yes
Voltage [V]	230
Frequency [Hz]	50/60
Power input [W]	176



designed for scientists

---

