

Reax top

Technical datasheet



Dimensions (W × H × D)	134 x 105 x 172 mm
Weight	2.8 kg
Maximum permissible load	n.a.
Drive	shaded pole motor
Speed range	100 – 2,500 rpm; 200 – 3,200 rpm
Protection class (EN 60529)	IP 22
Acoustic pressure	< 50 up to 2,500 rpm; < 58 up to 3,200 rpm
Rated voltage	230 V 50 Hz; 230 V 60 Hz; 115 V 60 Hz
Protection class	1
Overvoltage category	n.a.
Degree of pollution	n.a.
Power input	51 W
Operating temperature	n.a.
Installation altitude	n.a.
Overheat protection	self-resetting
Speed control	scale with reference points
Usable area	n.a.
Motion	circular vibrating
Orbit	5 mm
Fuse	n.a.
Permissible mains voltage fluctuations	n.a.

Bottle dimensions

n.a.