


Technical Specifications

Supply voltage variants	230 V 50 Hz
	115 V 60 Hz
Power input	7 W
Protection class (IEC 61140)	2 
Protection class (IEC 60529)	IP 21
Acoustic pressure (dB(A))	< 70 (in accordance with IEC 61010)
Drive	shaded pole motor
Operating mode	continuous
Speed range	0 – 2.200 rpm
Speed accuracy	±5 %
Max. stirring capacity (H ₂ O)	5 l
Max. load	6 kg
∅ stirrer plate	104 mm
Weight	1.1 kg
Dimensions (W × H × D)	126 × 80 × 140 mm

Scope of delivery

Component / Variants	Quantity	Product number
Hei-Mix S	1	503-02000-00
Operating instructions English / German	1	01-005-004-60
Guarantee registration / Declaration of no objection	1	01-006-002-78
EC Declaration of Conformity	1	01-001-025-06
Power supply cord	1	country specific

* The product numbers shown are for 230 V EU devices. For product numbers of variants, please contact Heidolph instruments.

Accessories



Accessories can be found on our homepage at www.heidolph-instruments.com