

This declaration of conformity is only valid for the instrument when it is:

- used in laboratory locations,
- used as delivered from Hoefer, Inc., except for alterations described in the user manual, and
- connected to other CE-labeled instruments or products recommended or approved by Hoefer, Inc.

3. Spécifications

Maximum Operating Ratings

Wattage	Heater: 800 W, thermostatically controlled
Pump Outlet	575 W
Power requirements	Model: 80-6428-84: 115 V~, 50/60 Hz 80-6429-03: 230 V~, 50/60 Hz

Environment

Operating environment:	Indoor use, 15–40 °C ambient Relative humidity ≤ 80% for 15–31 °C, decreasing linearly to 50% for 31–40 °C Altitude ≤ 2000 m Installation category II Pollution Degree 2
------------------------	--

Dimensions (w × d × h)	55.0 × 43.5 × 8.5 cm (21.6 × 17 × 3.4 in.)
----------------------------------	---

Weight	8 kg (17.6 lbs)
---------------	-----------------

Product certifications	CE, UL61010A-1, CSA
-------------------------------	---------------------