

Specifications

Power requirement	Frequency, 50–60 Hz Line voltage, 100–240 VAC 288 VA
User interface	3 digit, red LED membrane keypad
Output	5–200 V, 1 V increment 0.01–2.00 A, 0.01 A increment 200 W maximum 4 pairs output jacks in parallel
Output connector	4-mm plugs
Timer	1–999 min, 1 min increment
Environmental operating conditions	Indoor use: 4–40 °C Relative humidity: 0–80% noncondensing Altitude: < 2000 m Pollution degree: 2 Installation category: II
Dimensions (h × w × d)	33.5 × 12.5 × 28 cm 13.2 × 4.9 × 11.0 in
Weight	2.4 kg (5.3 lb)
Safety protection circuits	Short circuit protection Open circuit protection
Product certifications	EN61010-1:2001, EN61326 A3:2003 Class B CE WEEE RoHS