

Specifications

Power requirement	Frequency, 50 –60 Hz Line voltage, 100 –240 VAC 144 VA
User interface	3 digit, red LED membrane keypad
Output	10 –300 V, 1 V increment 4 –500 mA, 1 mA increment 90 W maximum 4 pairs output jacks in parallel
Output connector	4-mm plugs
Timer	1–999 min, 1 min increment
Environmental operating conditions	Indoor use: 4 –40 °C Relative humidity: 0 –80% noncondensing Altitude: <2000 m Pollution degree: 2 Installation category: II
Dimensions (h × w × d)	33.5 × 12.5 × 28 cm 13.2 × 4.9 × 11.0 in
Weight	2.4 kg (5.3 lb)
Safety protection circuits	Short circuit protection Open circuit protection
Product certifications	EN61010-1:2001, EN61326 A3:2003 Class B CE WEEE RoHS