

## Specifications

<b>Power requirement</b>	Frequency, 50–60 Hz Line voltage, 90–260 VAC
<b>User interface</b>	3 digit, red LED membrane keypad
<b>Output</b>	5–600 V, 1 V increment 3–750 mA, 1 mA increment 150 W maximum 4 pairs output jacks in parallel
<b>Output connector</b>	4 mm plugs
<b>Timer</b>	1–999 min, 1 min increment
<b>Environmental operating conditions</b>	Indoor use: 0–40 °C Relative humidity: 0–80% noncondensing Altitude: < 2000 m Pollution degree: 2 Installation category: II
<b>Dimensions (h × w × d)</b>	33.5 × 12.5 × 28 cm 13.2 × 4.9 × 11.0 in
<b>Weight</b>	2.4 kg (5.3 lb)
<b>Safety protection circuits</b>	Short circuit protection Open circuit protection
<b>Product certifications</b>	EN61010-1:2010, EN61326-1:2006 Class B CE WEEE RoHS