

2. Specifications

| | |
|------------------------------------|---|
| Gel plate size | 10 × 8 cm |
| Approximate gel size | 8 × 7 cm |
| Max. wattage | 12 W |
| Max. voltage | 500 V |
| Max. amperage | 500 mA |
| Max. temperature | 45 °C |
| Environmental operating conditions | Indoor use: 4–40 °C Humidity up to 80% Altitude up to 2000 m Installation category II Pollution degree II |
| Dimensions (w × h × d) | 16.5 × 16 × 16 cm (6.5 × 6.3 × 6.3 in.) |
| Product certifications | EN 61010-1, UL 61010A-1, CSA C22.2 1010.1, CE Certified |

This declaration of conformity is only valid for the instrument when it is:

- used in laboratory locations,
- used as delivered from Hoefer, Inc. except for alterations described in the user manual, and
- connected to other CE-labeled instruments or products recommended or approved by Hoefer, Inc.