

Specifications

Glass plate size	SE400: 18 × 16 cm SE410: 18 × 24 cm
Approximate gel size	SE400: 14 × 15 cm SE410: 14 × 23 cm
Max. wattage	20 W
Max. voltage	500 V at 40 mA
Max. amperage	30 mA/gel (60 mA total at 325 V)
Max. temperature	45 °C
Environmental operating conditions	Indoor use: 4–40 °C Humidity up to 80% Altitude up to 2000 m Installation category: II Pollution degree: II
Dimensions (w × h × d)	SE400: 24 × 28 × 15 cm (9.5 × 11 × 6 in.) SE410: 24 × 36 × 15 cm (9.5 × 14.2 × 6 in.)
Product certifications	EN61010–1, UL3101–1, CSA, C22.2 1010.1, CE

This declaration of conformity is only valid for the instrument when it is:

- used in laboratory locations,
- used as delivered from Hoefer, Inc. except for alterations described in the user manual, and
- connected to other CE-labeled instruments or products recommended or approved by Hoefer, Inc.