

Specifications

Gel plate size	18 × 16 cm (w × h)
Gel size	14 or 16 cm × 16 cm (w × h)
Maximum watt	50 W
Maximum volt	1000 V
Maximum amperage	500 mA
Maximum temperature	45 °C
Environmental operating conditions:	Indoor use: 4–40 °C Humidity up to 80% Altitude up to 2000 m Installation category: II Pollution degree: 2
Dimensions (w × h × d)	32 × 29 × 14 cm (12.5 × 11.5 × 5.5 in)
Product certifications	EN 61010-1, UL 61010A-1, CSA C22.2 1010.1, CE Certified

This declaration of conformity is valid only when the instrument is:

- used in laboratory locations,
- used as delivered from Hoefer, Inc. except for alterations described in the user manual, and
- connected to other CE-labeled instruments or products recommended or approved by Hoefer, Inc.