

Specifications

Gel plate size (w × h):	18 × 8 cm
Gel size:	14 × 8 cm
Maximum watt:	50 W
Maximum volt:	1000 V
Maximum ampere:	500 mA
Maximum temperature:	45 °C
Environmental operating conditions:	Indoor use: 4–40 °C Humidity up to 80% Altitude up to 2000 m Installation category: II Pollution degree: 2
Dimensions (w × h × d):	32 × 22.5 × 14 cm (12.5 × 8.75 × 5.5 in.)
Product certifications:	EN61010-1, UL61010A-1, CSA C22.2 1010.1, CE Certified

This declaration of conformity is only valid for the instrument when it is:

- used in laboratory locations,
- used as delivered from Hoefer, Inc. except for alterations described in the user manual, and
- connected to other CE-labeled instruments or products recommended or approved by Hoefer, Inc.