

Specifications

This declaration of conformity is only valid for the instrument when it is:

- used in laboratory locations,
- used as delivered from Hoefer, Inc. except for alterations described in the User Manual, and
- connected to other CE labeled instruments or products recommended or approved by Hoefer, Inc.

Gel size	up to four 9 × 10 cm gels
Max. wattage	50 W
Max. voltage	100 V
Max. amperage	500 mA
Max. temperature	45 °C
Buffer required	1.5 liters, depending on the number of cassettes in place
Environmental operating conditions	Indoor use: 4–40 °C Humidity up to 80% Altitude up to 2000 m Installation category II Pollution degree 2
Dimensions (w × h × d)	14 × 24 × 16.5 cm (5.5 × 9.5 × 6.5 in)
Product certifications	EN61010–1, UL3101–1, CSA C22.2 1010.1, CE