



designed for scientists



C 3000 isoperibol Package 1/10

/// Data Sheet

The IKA C 3000 isoperibol calorimeter is the technologically advanced successor of the IKA C 2000 model, with great new features such as faster sample runs, a spherically shaped decomposition vessel for faster heat transfer and a convenient touch screen for easy operation. Both oxygen filling and water handling are fully automated.

Its measurements and calculations of net calorific value are according to ISO 1928, ASTM D4809, ASTM D5865, ASTM 240 and GB T213. Areas of application include the power and cement industry where accurate analyses are vital.

Key features:



designed for scientists

- Easy handling via touch screen operation or standard USB mouse
- Two choices of starting temperatures (22°C, 30°C)
- Automated ignition, water filling and draining and oxygen filling
- Several interfaces: Ethernet, RS 232, USB, SD card slot
- Six temperature sensors to monitor all temperatures allowing best analysis
- Spherically shaped decomposition vessel for better pressure stability and faster heat transfer
- Easy sample preparation due to new crucible holder technology
- Can be operated with a chiller (e.g. RC 2 basic)

It includes:

- C 3000 measuring cell
- C 6010 decomposition vessel, standard
- RC 2 basic recirculation chiller
- Wear parts and consumables for up to 500 tests

Technical Data

Measuring range max. [J]	40000
Measuring mode dynamic 22°C	yes
Measuring mode isoperibol 22°C	yes
Measuring mode dynamic 30°C	yes
Measuring mode isoperibol 30°C	yes
Measurements/h dynamic	6
Measurements/h isoperibol	4
Reproducibility dynamic (1g benzoic acid NBS39i) [%RSD]	0.15
Reproducibility isoperibol (1g benzoic acid NBS39i) [%RSD]	0.05
Touchscreen	yes
Working temperature [°C]	22 - 30
Temperature measurement resolution [K]	0.0001
Cooling medium temperature [°C]	12 - 27
Cooling medium permissible operating pressure [bar]	1.5
Cooling medium	tap water
Type of cooling	flow
Chiller	RC 2 basic
Flow rate [l/h]	60 - 70
Rec. flow rate at 18°C [l/h]	60
Oxygen operating pressure max. [bar]	40
Interface scale	RS232
Interface printer	USB
Interface PC	RS232
Interface ext. keyboard	yes
Oxygen filling	yes
Decomposition vessel C 6010	yes
Decomposition vessel C 6012	yes
Analysis according to ASTM D240	yes
Analysis according to ASTM D4809	yes
Analysis according to ASTM D5865	yes
Analysis according to ISO 1928	yes
Analysis according to GB T213	yes
Works according to DIN 51900	yes
Works according to DIN EN ISO 1716	yes
Works according to DIN EN ISO 9831	yes
Works according to DIN EN ISO 18125	yes
Works according to DIN EN 15170	yes
Works according to DIN EN 15400	yes
Works according to DIN CEN TS 14918	yes
Works according to DIN CEN/TS 16023	yes
Works according to DIN SPEC 19524	yes
Works according to ASTM D240	yes
Works according to ASTM D4809	yes
Works according to ASTM D5468	yes
Works according to ASTM D5865	yes
Works according to ISO 1928	yes
Works according to GB T213	yes
Dimensions (W x H x D) [mm]	500 x 425 x 450



designed for scientists

Weight [kg]	29
Permissible ambient temperature [°C]	20 - 30
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 20
RS 232 interface	yes
USB interface	USB-B
Voltage [V]	100 - 120
Frequency [Hz]	50/60
Power input [W]	1700