

IKA

designed for scientists



Hula Dancer digital

/// Data Sheet

Hula Dancer digital is a powerful orbital shaker with robust housing for high stability. The device has a shaking diameter of 4.5 mm and allows a maximum load of 100g. Its speed range is from 1200 to 2800 rpm.



designed for scientists

Technical Data

Type of movement	orbital
Shaking stroke [mm]	4.5
Permissible shaking weight (incl. attachment) [kg]	0.1
Motor rating input [W]	9.5
Motor rating output [W]	5
Permissible ON time [%]	100
Speed min (adjustable) [rpm]	1200
Speed max. [rpm]	2800
Speed display	none
Timer display	none
Touch function	yes
Dimensions (W x H x D) [mm]	123 x 42 x 123
Weight [kg]	0.7
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 42
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input standby [W]	0.8