



MF 10.1 Cutting-grinding head

/// Data Sheet

For crushing fibrous substances such as paper and vegetation, but also for plastics and material with a low volume weight. Before being discharged, the ground material passes through a sieve. This sieve is interchangeable and available in different hole sizes (not incl. with delivery). The ground material can then be collected using an NS 29 standard ground vessel.



designed for scientists

Technical Data

Process type	inline
Circumferential speed max. [m/s]	24.5
Feed grain size max. [mm]	15
Material milling chamber	stainless steel 1.4308
Dimensions (W x H x D) [mm]	320 x 560 x 300
Weight [kg]	2.633
Permissible ambient temperature [°C]	5 - 40