



designed for scientists



## MICROSTAR 30 control

/// Data Sheet

The new MICROSTARS series by IKA: Developed using the latest cutting-edge technology, this high-tech overhead stirrer with its compact design is ideal for special applications.

Combining high performance with particular excellence, they require minimum space and come with a lifetime guarantee. See for yourself:

“The Strong One” in the smallest high-tech class, reaches up to 500 RPM!

- Hardened glass enclosed, fast response display for maximum visibility and chemical resistance

[www.ika.com](http://www.ika.com)

Subject to technical changes





designed for scientists

- State-of-art vibration sensors detect deviations from permissible thresholds and automatically stop the process
- Clear display for all essential information at a glance
- Integrated timer / counter for the control of kinetic sensitive reactions and reminders
- Viscosities up to 20,000 mPas and volumes of up to 20 l
- Continuously adjustable speed between 0/30 – 500 rpm
- USB interface, e.g. for documenting parameters using labworldsoft® or installing firmware updates
- Intuitive and simple handling; touch-sensitive surface for long service life
- Temperature reading on display
- Chemical resistant housing
- Key lock function
- Microprocessor-controlled speed governor for constant rotational speed, even with changes in viscosity

## Technical Data

Stirring quantity max. per stirring position (H2O) [l]	20
Motor rating input [W]	32
Motor rating output [W]	22
Motor principle	Brushless DC
Speed display	LCD
Speed range [rpm]	0/30 - 500
Viscosity max. [mPas]	20000
Output max. at stirring shaft [W]	15.7
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	30
Speed adjustment	Turning knob
Setting accuracy speed [rpm]	±1
Deviation of speed measurement n gt; 300rpm [%]	±1
Deviation of speed measurement n lt; 300rpm [rpm]	±3
Stirring element fastening	chuck
Connection for ext. temperature sensor	PT1000
Temperature display	yes
Chuck range diameter [mm]	0.5 - 8.2
Hollow shaft, inner diameter [mm]	8.5
Hollow shaft (push-through - when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	13
Extension arm length [mm]	160
Torque display	yes
Speed control	electronic
Nominal torque [Nm]	0.3
Torque measurement	trend
Deviation of torque measurement I [Ncm]	±3
Timer	yes
Timer display	LCD
Time setting range [min]	0 - 6000
Temperature measuring range [°C]	-10 - 350
Temperature measurement resolution [K]	0.1
Accuracy of temperature measurement [K]	±0.5 + tolerance PT1000 (DIN EN 60751 Class A)
Limit deviation temperature sensor [K]	≤ ± (0.15 + 0.002x T )
Housing material	alu-cast coating / thermoplastic polymer
Dimensions (W x H x D) [mm]	60 x 173 x 136
Weight [kg]	1.26
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 54
USB interface	yes
Bluetooth interface	yes
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	32
DC Voltage [V=]	24
Current consumption [mA]	1300

# IKA

designed for scientists

---