

IKA

designed for scientists



Mini MR standard

/// Data Sheet

Small magnetic stirrer without heating.

- For stirring quantities up to 1.000 ml (H₂O)
- Infinitely variable speed from 0 - 2.500 rpm
- White set-up plate suitable for observing color reactions



designed for scientists

Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H ₂ O) [l]	1
Maximum load [kg]	2
Motor rating output [W]	2
Direction of rotation	right
Speed adjustment	Turning knob
Speed range [rpm]	0 - 2500
Stirring bar length [mm]	20 - 40
Set-up plate material	polyester
Set-up plate dimensions [mm]	115 x 115
Dimensions (W x H x D) [mm]	115 x 37 x 129
Weight [kg]	0.22
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 42
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	3
DC Voltage [V=]	12
Current consumption [mA]	300