

CORIO CP-450F Refrigerated / heating circulator

Refrigerated circulators from the CORIO CP range are suitable for applications with a temperature range up to +200°C. The enhanced pump performance ensures they are suitable for easy temperature control tasks in combination with external applications.

Alternatively with natural refrigerant

The CORIO CP-450F is alternatively available with natural refrigerant. Order No. 9 013 714.N1



Product features

- Models for internal and external applications
- Bright, white, easy to read display
- Very quiet
- Easy pump change-over between internal and external circulation
- External pump connections
- Powerful and infinitely adjustable pressure pump
- USB connection
- RS232 interface for online communication
- Space-saving cooling coil design provides more usable space in the bath tank
- Bath lid and drain tap included
- Removable ventilation grid
- Refrigeration unit without side vents
- Unique early warning system for low liquid level
- Class III (FL) according to DIN 12876-1

Performance values

115V/60Hz (Nema N5-15 Plug)	
Heating capacity kW	1
Viscosity max. cST	50
Pump capacity flow rate l/min	8 ... 27
Pump capacity flow pressure psi	1.5 ... 10.2
Power A	12

Refrigerant variants

Order No. 9013714.N1.02

Cooling capacity (Ethanol)

°C	20	0	-10	-20	-30
kW	0.44	0.37	0.27	0.16	0.06

*Performance specifications measured in accordance with DIN12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

Refrigerant stage 1

Refrigerant R290

Filling volume g 31

Global Warming Potential for R290 3

Carbon dioxide equivalent t 0

Order No. 9013714.S1.02

Cooling capacity (Ethanol)

°C	20	0	-10	-20	-30
kW	0.44	0.37	0.27	0.16	0.06

*Performance specifications measured in accordance with DIN12876. Cooling capacities up to 20 °C measured with ethanol; over 20 °C with thermal oil unless otherwise specified. Performance specifications apply at an ambient temperature of 20 °C. Performance values may differ with other bath fluids.

Refrigerant stage 1

Refrigerant R449A

Filling volume g 70

Global Warming Potential for R449A 1397

Carbon dioxide equivalent t 0.098

Technical data

Available voltage versions		Bath	
Order No.	9 013 714	Bath tank	Stainless steel
Available voltage versions:		Bath cover	integrated
9013714.N1.01	100V/50-60Hz (Nema N5-15 Plug) (R290)	Usable bath opening in. (W x L / D)	5.1 x 5.9 / 5.9
9013714.S1.01	100V/50-60Hz (Nema N5-15 Plug) (R449A)		
9013714.N1.02	115V/60Hz (Nema N5-15 Plug) (R290)		
9013714.S1.02	115V/60Hz (Nema N5-15 Plug) (R449A)		
9013714.N1.33	200-230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F) (R290)		
9013714.S1.33	200-230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F) (R449A)		

9013714.N1.33.chn	200-230V/50-60Hz (CN Plug) (R290)
9013714.S1.33.chn	200-230V/50-60Hz (CN Plug) (R449A)
9013714.N1.04	200-230V/50-60Hz (UK Plug Type BS1363A) (R290)
9013714.S1.04	200-230V/50-60Hz (UK Plug Type BS1363A) (R449A)
9013714.N1.05	200-230V/50-60Hz (CH Plug Type SEV 1011) (R290)
9013714.S1.05	200-230V/50-60Hz (CH Plug Type SEV 1011) (R449A)

Cooling

Cooling of compressor	1-stage Air
-----------------------	-------------

Other

Classification	Classification III (FL)
IP Code	IP 21
Pump function	Pressure Pump
Pump type	Immersion Pump

Electronics

Digital interface	RS232, USB
Temperature control	PID1
Absolute temperature calibration	3 Point Calibration
Temperature display	LED
Temperature setting	Keypad
Electronic Timer hr:min	0 ... 999

Dimensions and volumes

Weight lbs	56.4
Barbed fittings inner diameter	8/12 mm
Dimensions in. (W x L x H)	9.1 x 15.7 x 25.6
Filling volume l	3 ... 4
Pump connections	M16x1 male

Temperature values

Working temperature range °C	-30 ... +200
Temperature stability °C	±0.03
Ambient temperature °C	+5 ... +40
Temperature display resolution °C	0.01 ... 0.1

Included in delivery

2 Barbed fittings for tubing 8 and 12 mm ID. (Pump connections M16x1 male)

All Benefits



Brilliant.
Very bright display makes it easy to read even from a distance.



Connection. Easy.
Inclined pump connections (M16x1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



Everything at the front.
All operating controls and safety functions are accessed easily and comfortably from the front.



Exact.
You can rely on it. PID1 control and 'Active Cooling Control' make the new CORIO precise and perfect.



Locked in.
The lockable power plug guarantees safe connection. More process safety.



Switch on. And off you go.
Intelligent operating concept. Ready for operation with just a few quick and easy steps.



Timer. Integrated.
CORIO circulators include an integrated timer function. When the set time has elapsed, a signal sounds and the device switches off. Setting range: 0 ... 999 minutes.



Powerful. Adjustable.
Strong pressure pump, continuously adjustable.



Early warning system for low liquid level.
Maximum safety for your application. Optical and audible alarm allows user to refill bath fluid in time.



Connectivity.
Remote control made easy. CORIO CP circulators feature a USB connection and RS232 interface.