

## PURA 14 Water Bath

PURA water baths stand for innovative, simple, and safe working in the laboratory. All models (except PURA 4) come with an integrated drain screw for quick and clean draining of the baths. PURA water baths are flexible and can be easily transported through ergonomic side recessed grips. Non-slip rubber feet ensure a firm footing and more safety in the laboratory.



### Your advantages

- Easy operation
- Bright display
- Mains switch is protected against spray water
- Integrated protection against running dry
- Integrated drain screw (except PURA 4)
- No distracting elements in the bath
- Platform included as standard
- Integrated timer
- Non-slip rubber feet
- Ergonomic recessed grips

### Technical data

<b>Available voltage versions</b>		<b>Bath</b>	
Order No.	9 550 514	Bath tank	Stainless steel
Available voltage versions:		Bath cover	accessory
9 550 514.22	100-115V/50-60Hz (Nema N5-15 Plug)	Usable bath opening in. (W x L / D)	13 x 10.6 / 5.5
9 550 514.33	230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F)		
9 550 514.04	230V/50-60Hz (UK Plug Type BS1363A)		
9 550 514.05	230V/50-60Hz (CH Plug Type SEV 1011)		
9 550 514.33.chn	230V/3PPE/50-60Hz (CN Plug)		
<b>Cooling</b>		<b>Other</b>	
Cooling coil	accessory	Classification	Classification I (NFL)
		IP Code	IP 21
<b>Electronics</b>		<b>Waterbath</b>	
Temperature display	LED	Insert capacity for test tube racks 13 mm ø pc.	270
Temperature setting	Keypad	Insert capacity for test tube racks 17 mm ø pc.	180
Electronic Timer hr:min	00:01 ... 99:59	Dimension with bathcover in. (W x L x H)	16.5 x 14.6 x 14.2
<b>Dimensions and volumes</b>		<b>Temperature values</b>	
Usable immersion depth in.	5.5	Setting the resolution of the temperature display °C	0.1
Weight lbs	18.7	Working temperature range °C	+18 ... +99.9
Dimensions in. (W x L x H)	16.5 x 13.8 x 8.7	Temperature stability °C	±0.15
Filling volume l	2 ... 14	Ambient temperature °C	5 ... 40
		Temperature display resolution °C	0.1

**Performance values**

100-115V/50-60Hz (Nema N5-15 Plug)

100V/50Hz		100V/60Hz	
Heating capacity kW	0.98	Heating capacity kW	0.98
115V/50Hz		115V/60Hz	
Heating capacity kW	1.3	Heating capacity kW	1.3

230V/50-60Hz (Schuko Plug - CEE 7/4 Plug Type F)

230V/50Hz		230V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8

230V/50-60Hz (UK Plug Type BS1363A)

230V/50Hz		230V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8

230V/50-60Hz (CH Plug Type SEV 1011)

230V/50Hz		230V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8

230V/3PPE/50-60Hz (CN Plug)

230V/50Hz		230V/60Hz	
Heating capacity kW	1.8	Heating capacity kW	1.8

**All Benefits**



**Less is more.**  
Thanks to their design, PURA water baths require a minimum amount of water so that even small sample containers stand safely.



**Lightweight.**  
PURA water baths impress with their low weight and can be flexibly used.



**Start. Stopp. Timer.**  
PURA water baths offer an internal timer function. After expiration of the set time, a signal sounds and the device either continues operation or switches off.



**Tilting – no, thank you.**  
The PURA water bath design is tiltproof. Non-slip rubber feet prevent slipping and carrying handles simplify the transport.



**Easy cleaning.**  
PURA does not incorporate any interfering functional elements. The smooth surfaces can be cleaned quickly and without residue.



**Ease of use.**  
The controls on the front side are easy to reach and use.



**Easy handling.**  
A frontally integrated drain screw allows clean, safe, and effortless emptying of the baths. (not PURA 4)



**Brilliant.**  
Very bright display makes it easy to read even from a distance.



**100% Checked.**  
100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



**Green technology.**  
Development consistently applied environmentally friendly materials and technologies.



**JULABO. Quality.**  
Highest standards of quality for a long product life.



**Quick start.**  
Individual JULABO consultation and comprehensive manuals at your disposal.



**Satisfied customers.**  
11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



**Services 24/7.**  
Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at [www.julabo.com](http://www.julabo.com).