

8. Associated standards and regulations

Construction in accordance with the following safety standards:
EN 61010-1
UL 3101-1
CAN/CSA C22.2(1010-1)
EN 61010-2-10
Construction in accordance with the following EMC standards:
EN 61326-1

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

NOTE: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

9. Specification

Items	Specifications
Voltage [VAC]	100-240
Frequency [Hz]	50/60
Motor rating input[W]	16
Motor rating output[W]	10
Motor type	DC motor
Speed range [rpm]	0-80
Shaking motion	Orbital
Dimensions[D×W×H mm]	300X220X310/150X530X190
Weight[kg]	2.0/1.7
Permissible ambient temperature[°C]	5-40
Permissible relative humidity	80%
Protection class acc.DIN EN60529	IP21