

## 10. Specifications

Items	Specifications
Voltage [VAC]	100~240
Frequency [Hz]	50/60
Power [W]	40
Angle range(MS-RO70)	0°~ 90°
Motor type	DC motor
Speed range [rpm]	10~70
Speed display	LCD
Timer range [min]	1~1199
Timer display	LCD
Run type	Timer/Continuous operation
Overall Dimensions [mm]	280×210×300(MS-RO70) 220×510×260(MS-RO70-T)
Weight [kg]	6.5
Permissible ambient temperature [°C]	5—40
Permissible relative humidity	80%
Protection class acc. to DIN EN60529	IP21

Table 4