





















Rotors for FRONTIER™ FC5916 and FC5916R

	Swing Out Rotor 2 × 3 MTP w/Bucket	
	Item No.	30314824
	Rotor Capacity	2 × 3 MTP
	Rotor Type	Swing Out, 0-90°
	Permissible Net Weight	2 × 310 g
	Lowest Temperature	-15 °C

Accessory Specifications		
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM (FC5916/FC5916R)	4,500	
Quantity in Package	2/pk	
Max. RCF	2,716 × g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42

	Angle Rotor 4 × 85 ml	
	Item No.	30314827
	Rotor Capacity	4 x 85 ml
	Rotor Type	Angle, 30°
	Permissible Net Weight	4 x 140 g
	Lowest Temperatures	4 °C




Accessory Specifications	n/a							
Accessory Item No.	n/a	30314893	30314894	30314895	30314896*	30314897*	30314898	30314899
Accessory Type	n/a	Adapter						
Max. RPM (FC5916/FC5916R)	15,000/16,000							
Quantity in Package	n/a	2/pk						
Max. RCF (FC5916/FC5916R)	23,685 / 26,331 × g	17,103 / 18,243 × g	16,902 / 18,028 × g	17,908 / 19,101 × g	17,304 / 18,457 × g	16,700 / 17,813 × g	15,091 / 16,097 × g	16,700 / 17,813 × g
Tube Specifications								
Tube Type	Round Bottom			Conical Bottom		Round Bottom		
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml
Tubes per Rotor	4				8		4	
Max. Tube Diameter (mm)	38	17	25	29		17		18
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110

*Only without rotor lid

Rotors for FRONTIER™ FC5830R


















Swing Out Rotor 2 x 3 MTP w/Bucket	
Item No.	30314824
Rotor Capacity	2 x 3 MTP
Rotor Type	Swing Out, 0-90°
Permissible Net Weight	2 x 310 g
Lowest Temperature	n/a

Accessory Specifications		
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM	4,500	
Quantity in Package	2/pk	
Max. RCF	2,716 x g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42













Angle Rotor 4 x 85 ml	
Item No.	30314827
Rotor Capacity	4 x 85 ml
Rotor Type	Angle, 30°
Permissible Net Weight	4 x 140 g
Lowest Temperatures	18 °C


Accessory Specifications	n/a							
Accessory Item No.	n/a	30314893	30314894	30314895	30314896*	30314897*	30314898	30314899
Accessory Type	n/a	Adapter						
Max. RPM	20,000							
Quantity in Package	n/a	2/pk						
Max. RCF	41,137 x g	38,007 x g	37,560 x g	39,896 x g	38,454 x g	37,113 x g	33,536 x g	37,113 x g
Tube Specifications								
Tube Type	Round Bottom				Conical Bottom		Round Bottom	
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml
Tubes per Rotor	4						8	4
Max. Tube Diameter (mm)	38	17	25	29		17		18
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110




*Only without rotor lid

Rotors for FRONTIER™ FC5816 and FC5816R

	Angle Rotor 30 × 15 ml	
	Item No.	30314832
	Rotor Capacity	30 x 15 ml
	Rotor Type	Angle, 35°
	Permissible Net Weight	30 x 32 g
	Lowest Temperatures	-8 °C

Accessory Specifications	n/a				
Accessory Item No.	n/a	30211180	30130886	30130889	30130890
Accessory Type	n/a	Adapter			
Max. RPM (FC5816/FC5816R)	4,500/4,500				
Quantity in Package	n/a	2/pk	6/pk	2/pk	
Max. RCF (FC5816/FC5816R)	2,830 x g	2,716 x g / 2,354 x g	2,038 x g	2,762 x g	2,377 x g
Tube Specifications					
Tube Type	Round Bottom/Conical Bottom	Vacutainer® / Sarstedt®	Microtube	Round Bottom/Vacutainer®	RIA/Vacutainer®/Sarstedt®
Tube Volume	15 ml	9-10ml	1.5/2.0 ml	7 ml	5 ml
Tubes per Rotor	30	20	30	20	
Max. Tube Diameter (mm)	17	16	11	13	
Tube Height (mm)	95/115	92-107	40	95/115	70/90




	Swing Out Rotor 2 × 3 MTP w/Bucket	
	Item No.	30314824
	Rotor Capacity	2 x 3 MTP
	Rotor Type	Swing Out, 0-90°
	Permissible Net Weight	2 x 310 g
	Lowest Temperatures	-3 °C

Accessory Specifications		
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM (FC5816/FC5816R)	4,500	
Quantity in Package	2/pk	
Max. RCF (FC5816/FC5816R)	2,716 x g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42

Rotors for FRONTIER™ FC5720R


















Swing Out Rotor 2 x 3 MTP w/Bucket	
Item No.	30314824
Rotor Capacity	2 x 3 MTP
Rotor Type	Swing Out, 0-90°
Permissible Net Weight	2 x 310 g
Lowest Temperature	-14°C

Accessory Specifications		
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM	4,500	
Quantity in Package	2/pk	
Max. RCF	2,716 x g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42







Angle Rotor 4 x 85 ml	
Item No.	30314827
Rotor Capacity	4 x 85 ml
Rotor Type	Angle, 30°
Permissible Net Weight	4 x 140 g
Lowest Temperatures	1 °C


Accessory Specifications	n/a							
Accessory Item No.	n/a	30314893	30314894	30314895	30314896*	30314897*	30314898	30314899
Accessory Type	n/a	Adapter						
Max. RPM	15,000							
Quantity in Package	n/a	2/pk						
Max. RCF	23,685 x g	17,103 x g	16,902 x g	17,908 x g	17,304 x g	16,700 x g	15,091 x g	16,700 x g
Tube Specifications								
Tube Type	Round Bottom				Conical Bottom		Round Bottom	
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml
Tubes per Rotor	4						8	4
Max. Tube Diameter (mm)	38	17	25	29		17		18
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110




*Only without rotor lid

Rotors for FRONTIER™ FC5718 and FC5718R

Accessory Specifications	 30314881	 30314882
Accessory Item No.	30314881	30314882
Accessory Type	Bucket	
Max. RPM (FC5718/FC5718R)	5,000	
Quantity in Package	2/pk	
Max. RCF (FC5718/FC5718R)	3,885 x g	
Tube Specifications		
Tube Type	Conical Bottom	
Tube volume	50 ml	15 ml
Tubes per Rotor	8	12
Max. Tube Diameter (mm)	29	17
Tube Height (mm)	116	120

*Only without bucket lid




	Swing Out Rotor 2 x 3 MTP w/Bucket	
Item No.	30314824	
Rotor Capacity	2 x 3 MTP	
Rotor Type	Swing Out, 0-90°	
Permissible Net Weight	2 x 310 g	
Lowest Temperatures	-5 °C	

Accessory Specifications	 30314890	 30314891
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM (FC5718/FC5718R)	4,500	
Quantity in Package	2/pk	
Max. RCF (FC5718/FC5718R)	2,716 x g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42

Rotors for FRONTIER™ FC5714
















Swing Out Rotor 2 x 3 MTP w/Bucket	
Item No.	30314824
Rotor Capacity	2 x 3 MTP
Rotor Type	Swing Out, 0-90°
Permissible Net Weight	2 x 310 g
Lowest Temperature	n/a

Accessory Specifications		
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM	4,500	
Quantity in Package	2/pk	
Max. RCF	2,716 x g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42



Angle Rotor 6 x 50 ml	
Item No.	30314830
Rotor Capacity	6 x 50 ml
Rotor Type	Angle, 40°
Permissible Net Weight	6 x 72 g
Lowest Temperature	n/a

Accessory Specifications	n/a						
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30130891	30130892	30130894
Accessory Type	n/a	Adapter					
Max. RPM	6,000						
Quantity in Package	n/a	6/pk	2/pk				
Max. RCF	4,427 x g	2,696 x g	4,105 x g	3,340 x g	4,306 x g	4,145 x g	4,266 x g
Tube Specifications							
Tube Type	Round Bottom/ Conical Bottom	Microtube	Round Bottom/ Vacutainer®	RIA/Vacutainer® / Sarstedt®	Round Bottom/Vacutainer®		Round Bottom/ Conical Bottom
Tube volume	50 ml	1.5/2.0 ml	7 ml	5 ml	30 ml	16 ml	15 ml
Tubes per Rotor	6						
Max. Tube Diameter (mm)	29	11	13		25	18	17
Tube Height (mm)	100/120	42	95/100	65/90	100	100/105	97/120

* only possible with adapter 30130894