




# Rotors for FRONTIER™ FC5916 and FC5916R


















Swing Out Rotor 2 × 3 MTP w/Bucket	
Item No.	30314824
Rotor Capacity	2 × 3 MTP
Rotor Type	Swing Out, 0-90°
Permissible Net Weight	2 × 310 g
Lowest Temperature	-15 °C

Accessory Specifications		
Accessory Item No.	30314890	30314891
Accessory Type	Bucket	Adapter
Max. RPM (FC5916/FC5916R)	4,500/4,500	
Quantity in Package	2/pk	
Max. RCF	2,716/2,716 × g	
Tube Specifications	n/a	
Tube Type	Microplate	Microtube
Tube volume	MTP	1.5/2.0 ml
Tubes per Rotor	6 Standard Microplates or 2 Deepwell Plates	96
Max. Tube Diameter (mm)	87 x 128	11
Tube Height (mm)	63	42



Angle Rotor 4 × 85 ml	
Item No.	30314827
Rotor Capacity	4 x 85 ml
Rotor Type	Angle, 30°
Permissible Net Weight	4 x 140 g
Lowest Temperatures	4 °C

Accessory Specifications	n/a							
Accessory Item No.	n/a	30314893	30314894	30314895	30314896*	30314897*	30314898	30314899
Accessory Type	n/a	Adapter						
Max. RPM (FC5916/FC5916R)	15,000/16,000							
Quantity in Package	n/a	2/pk						
Max. RCF (FC5916/FC5916R)	23,685 / 26,331 × g	17,103 / 18,243 × g	16,902 / 18,028 × g	17,908 / 19,101 × g	17,304 / 18,457 × g	16,700 / 17,813 × g	15,091 / 16,097 × g	16,700 / 17,813 × g
Tube Specifications								
Tube Type	Round Bottom			Conical Bottom		Round Bottom		
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml
Tubes per Rotor	4						8	4
Max. Tube Diameter (mm)	38	17	25	29		17		18
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110

\*Only without rotor lid