





































Rotors for FRONTIER™ FC5816 and FC5816R

Accessory Specifications							
Accessory Item No.	30314906	30314907	30314908	30314909	30314910	30314911	30314912
Accessory Type	Rack						
Max. RPM (FC5816/FC5816R)	4,500/4,500						
Quantity in Package	2/pk						
Max. RCF	3,780 x g	3,576 x g		3,644 x g		3,508 x g	3,689 x g
Tube Specifications							
Tube Type	Conical Bottom	Round Bottom	Skirted Conical Bottom		Round Bottom	Skirted Conical Bottom	Round Bottom
Tube volume	50 ml				25 ml		15 ml
Tubes per Rotor	12	4	8	4	20	12	36
Max. Tube Diameter (mm)	29	34	29		24.5		17
Tube Height (mm)	116	100/120		116	100/120	85/100	76/115

Accessory Specifications					
Accessory Item No.	30314913	30314914	30314915	30314916	30314917
Accessory Type	Rack				
Max. RPM (FC5816/FC5816R)	4,500/4,500				
Quantity in Package	2/pk				
Max. RCF	3,712 x g	3,644 x g	3,689 x g	3,599 x g	
Tube Specifications					
Tube Type	Conical Bottom	Skirted Conical Bottom	Round Bottom		Vacutainer®/Sarstedt®
Tube Volume	15 ml		10 ml	5-7 ml	1.6-7 ml
Tubes per Rotor	28		32	56	40
Max. Tube Diameter (mm)	17		16	13	
Tube Height (mm)	95/120	100/120	80/100	65/120	65/100



Swing Out Rotor 4 x 250 ml	
Item No.	30314828
Rotor Capacity	4 x 250 ml
Rotor Type	Swing Out, 0-90°
Permissible Net Weight	4 x 557 g
Lowest Temperatures	2 °C

Accessory Specifications						
Accessory Item No.	83041039	30304375	30314583	30314584	30314585	83041038
Accessory Type	Rack					
Max. RPM (FC5816/FC5816R)	4,500/4,500					
Quantity in Package	2/pk					
Max. RCF	3,531 x g	3,735 x g		3,599 x g	3,531 x g	3,577 x g
Tube Specifications						
Tube Type	Flat Bottom	Conical Bottom		Vacutainer® / Sarstedt®		Sarstedt®
Tube Volume	250 ml	50 ml	15 ml	5-7 ml	4-10 ml	1.1-5 ml
Tubes per Rotor	4	16	40	56	48	72
Max. Tube Diameter (mm)	62	29	17	13	16	11
Tube Height (mm)	122	116	120	75/100		92