

Rotors for FRONTIER™ FC5917RF and FC5917RF Under Bench



Angle Rotor 4 x 85 ml	
Item No.	30314827
Rotor Capacity	4 x 85 ml
Rotor Type	Angle, 30°
Permissible Net Weight	4 x 140 g
Lowest Temperatures	-2°C

Accessory Specifications	n/a							
Accessory Item No.	n/a	30314893	30314894	30314895	30314896*	30314897*	30314898	30314899
Accessory Type	n/a	Adapter						
Max. RPM	16,010 rpm							
Quantity in Package	n/a	2p/k						
Max. RCF	26,361 x g	24,355 x g	24,069 x g	25,501 x g	24,642 x g	23,782 x g	21,490 x g	23,782 x g
Tube Specifications								
Tube Type	Round Bottom				Conical Bottom		Round Bottom	
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml
Tubes per Rotor	4						8	4
Max. Tube Diameter (mm)	38	17	25	29		17		18
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110

*Only without rotor lid



Angle Rotor 10 x 50 ml	
Item No.	30314829
Rotor Capacity	10 x 50 ml
Rotor Type	Angle, 38°
Permissible Net Weight	10 x 76 g
Lowest Temperatures	1°C

Accessory Specifications	n/a					
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30472300	30472307
Accessory Type	n/a	Adapter				
Max. RPM	10,500 rpm					
Quantity in Package	n/a	6/pk	2p/k			
Max. RCF	16,022 x g	10,229 g	14,050 x g	12,078 x g	15,652 x g	15,775 x g
Tube Specifications						
Tube Type	Conical Bottom	Microtube	Round Bottom/ Vacutainer®	RIA/Vacutainer®/ Sarstedt®	Round Bottom/ Vacutainer®	Conical Bottom
Tube volume	50 ml	1.5/2.0 ml	7 ml	5 ml	15 ml	
Tubes per Rotor	10					
Max. Tube Diameter (mm)	29	11	13			17
Tube Height (mm)	116	40	95/115	70/90	97/123	120

*Only possible with adapter 30472300 or 30472307

Rotors for FRONTIER™ FC5916 and FC5916R



Angle Rotor 6 × 85 ml	
Item No.	30314826
Rotor Capacity	6 × 85 ml
Rotor Type	Angle, 38°
Permissible Net Weight	6 × 140 g
Lowest Temperatures	2 °C

Accessory Specifications	n/a								
Accessory Item No.	n/a	30314893	30314894	30314895	30314896	30314897	30314898	30314899	
Accessory Type	n/a	Adapter							
Max. RPM (FC5916/FC5916R)	11,000/13,000								
Quantity in Package	n/a	2/pk							
Max. RCF (FC5916/FC5916R)	15,555 / 21,762 × g	14,338 / 20,025 × g	14,067 / 19,647 × g	14,743 / 20,592 × g	14,338 / 20,025 × g	14,067 / 19,647 × g	15,014 / 20,970 × g	14,067 / 19,647 × g	
Tube Specifications									
Tube Type	Round Bottom			Conical Bottom		Round Bottom			
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml	
Tubes per Rotor	6						12		6
Max. Tube Diameter (mm)	38	17	25	29		17		18	
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110	



Angle Rotor 10 × 50 ml	
Item No.	30314829
Rotor Capacity	10 × 50 ml
Rotor Type	Angle, 38°
Permissible Net Weight	10 × 76 g
Lowest Temperatures	0 °C

Accessory Specifications	n/a					
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30472300	30472307
Accessory Type	n/a	Adapter				
Max. RPM (FC5916/FC5916R)	10,000/10,500					
Quantity in Package	n/a	6/pk	2/pk			
Max. RCF (FC5916/FC5916R)	14,532 / 16,022 × g	9,278 / 10,229 × g	12,774 / 14,050 × g	10,955 / 12,078 × g	14,197 / 15,652 × g	14,309 / 15,775 × g
Tube Specifications						
Tube Type	Conical Bottom	Microtube	Round Bottom/ Vacutainer®	RIA (Radioimmuno- assay)/Vacutainer®/ Sarstedt®	Round Bottom/ Vacutainer®	Conical Bottom
Tube Volume	50 ml	1.5/2.0 ml	7 ml	5 ml	15 ml	
Tubes per Rotor	10					
Max. Tube Diameter (mm)	29	11	13		17	
Tube Height (mm)	116	40	95/115	65/75	97/123	120

*Only possible with adapter 30472300 or 30472307

Rotors for FRONTIER™ FC5830R



Angle Rotor 10 x 50 ml	
Item No.	30314829
Rotor Capacity	10 x 50 ml
Rotor Type	Angle, 38°
Permissible Net Weight	10 x 76 g
Lowest Temperatures	-4 °C

Accessory Specifications	n/a					
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30472300	30472307
Accessory Type	n/a	Adapter				
Max. RPM	10,500					
Quantity in Package	n/a	6/pk	2/pk			
Max. RCF	16,022 x g	10,229 x g	14,050 x g	12,078 x g	12,078 x g	15,775 x g
Tube Specifications						
Tube Type	Conical Bottom	Microtube	Round Bottom/ Vacutainer®	RIA (Radioimmuno- assay)/Vacutainer®/ Sarstedt®	Round Bottom/ Vacutainer®	Conical Bottom
Tube Volume	50 ml	1.5/2.0 ml	7 ml	5 ml	15 ml	
Tubes per Rotor	10					
Max. Tube Diameter (mm)	29	11	13		17	
Tube Height (mm)	116	40	95/115	65/75	97/123	120

*Only possible with adapter 30472300 or 30472307



Angle Rotor 30 x 15 ml	
Item No.	30314832
Rotor Capacity	30 x 15 ml
Rotor Type	Angle, 35°
Permissible Net Weight	30 x 32 g
Lowest Temperatures	-20 °C

Accessory Specifications	n/a				
Accessory Item No.	n/a	30211180	30130886	30130889	30130890
Accessory Type	n/a	Adapter			
Max. RPM	4,500				
Quantity in Package	n/a	2/pk	6/pk	2/pk	
Max. RCF	2,830 x g	2,716 x g / 2,354 x g	2,038 x g	2,762 x g	2,377 x g
Tube Specifications					
Tube Type	Round Bottom/Conical Bottom	Vacutainer® / Sarstedt®	Microtube	Round Bottom/Vacutainer®	RIA/Vacutainer®/Sarstedt®
Tube Volume	15 ml	9-10ml	1.5/2.0 ml	7 ml	5 ml
Tubes per Rotor	30	20	30	20	
Max. Tube Diameter (mm)	17	16	11	13	
Tube Height (mm)	95/120	92-107	40	95/115	65/75

Rotors for FRONTIER™ FC5816 and FC5816R



Angle Rotor 6 × 85 ml	
Item No.	30314826
Rotor Capacity	6 x 85ml
Rotor Type	Angle, 38°
Permissible Net Weight	6 x 140 g
Lowest Temperatures	15 °C

Accessory Specifications	n/a							
Accessory Item No.	n/a	30314893	30314894	30314895	30314896	30314897	30314898	30314899
Accessory Type	n/a	Adapter						
Max. RPM (FC5816/FC5816R)	11,000/13,000							
Quantity in Package	n/a	2/pk						
Max. RCF (FC5816/FC5816R)	15,555 /21,762 x g	14,338 /20,025 x g	14,067 /19,647 x g	14,743 /20,592 x g	14,338 /20,025 x g	14,067 /19,647 x g	15,014 /20,970 x g	14,067 /19,647 x g
Tube Specifications								
Tube Type	Round Bottom			Conical Bottom		Round Bottom		
Tube volume	85 ml	15 ml	30 ml	50 ml		15 ml		16 ml
Tubes per Rotor	6						12	6
Max. Tube Diameter (mm)	38	17	25	29		17		18
Tube Height (mm)	113	103/110	90/103	105	116	120	95/100	103/110



Angle Rotor 10 × 50 ml	
Item No.	30314829
Rotor Capacity	10 x 50 ml
Rotor Type	Angle, 38°
Permissible Net Weight	10 x 76 g
Lowest Temperatures	9 °C

Accessory Specifications	n/a					
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30472300	30472307
Accessory Type	n/a	Adapter				
Max. RPM (FC5816/FC5816R)	9,000/10,500					
Quantity in Package	n/a	6/pk	2/pk			
Max. RCF (FC5816/FC5816R)	11,771 / 16,022 x g	7,515 / 10,229 x g	10,322 / 14,050 x g	8,874 / 12,078 x g	11,499 / 15,652 x g	11,590 / 15,775 x g
Tube Specifications						
Tube Type	Conical Bottom	Microtube	Round Bottom/ Vacutainer®	RIA/Vacutainer®/ Sarstedt®	Round Bottom/ Vacutainer®	Conical Bottom
Tube Volume	50 ml	1.5/2.0 ml	7 ml	5 ml	15 ml	
Tubes per Rotor	10					
Max. Tube Diameter (mm)	29	11	13		17	
Tube Height (mm)	116	40	95/115	65/75	97/123	120

*Only possible with adapter 30472300 or 30472307

Rotors for FRONTIER™ FC5720R



Angle Rotor 10 x 50 ml	
Item No.	30314829
Rotor Capacity	10 x 50 ml
Rotor Type	Angle, 38°
Permissible Net Weight	10 x 76 g
Lowest Temperatures	-6 °C

Accessory Specifications	n/a					
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30472300	30472307
Accessory Type	n/a	Adapter				
Max. RPM	9,000					
Quantity in Package	n/a	6/pk	2/pk			
Max. RCF	11,771 x g	7,515 x g	10,322 x g	8,874 x g	11,499 x g	11,590 x g
Tube Specifications						
Tube Type	Conical Bottom	Microtube	Round Bottom/ Vacutainer®	RIA (Radioimmuno- assay)/Vacutainer®/ Sarstedt®	Round Bottom/ Vacutainer®	Conical Bottom
Tube Volume	50 ml	1.5/2.0 ml	7 ml	5 ml	15 ml	
Tubes per Rotor	10					
Max. Tube Diameter (mm)	29	11	13		17	
Tube Height (mm)	116	40	95/115	65/75	97/123	120

*Only possible with adapter 30472300 or 30472307



Angle Rotor 30 x 15 ml	
Item No.	30314832
Rotor Capacity	30 x 15 ml
Rotor Type	Angle, 35°
Permissible Net Weight	30 x 32 g
Lowest Temperatures	-8 °C

Accessory Specifications	n/a				
Accessory Item No.	n/a	30211180	30130886	30130889	30130890
Accessory Type	n/a	Adapter			
Max. RPM	4,500				
Quantity in Package	n/a	2/pk	6/pk	2/pk	
Max. RCF	2,830 x g	2,716 x g / 2,354 x g	2,038 x g	2,762 x g	2,377 x g
Tube Specifications					
Tube Type	Round Bottom/Conical Bottom	Vacutainer® / Sarstedt®	Microtube	Round Bottom/Vacutainer®	RIA/Vacutainer®/Sarstedt®
Tube Volume	15 ml	9-10ml	1.5/2.0 ml	7 ml	5 ml
Tubes per Rotor	30	20	30	20	
Max. Tube Diameter (mm)	17	16	11	13	
Tube Height (mm)	95/120	92-107	40	95/115	65/75

Rotors for FRONTIER™ FC5718 and FC5718R



Angle Rotor 10 x 50 ml	
Item No.	30314829
Rotor Capacity	10 x 50 ml
Rotor Type	Angle, 38°
Permissible Net Weight	10 x 76 g
Lowest Temperatures	0 °C

Accessory Specifications	n/a					
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30472300	30472307
Accessory Type	n/a	Adapter				
Max. RPM (FC5718/FC5718R)	7,500					
Quantity in Package	n/a	6/pk	2/pk			
Max. RCF (FC5718/FC5718R)	8,174 x g	5,219 x g	7,168 x g	6,192 x g	7,986 x g	8,049 x g
Tube Specifications						
Tube Type	Conical Bottom	Microtube	Round Bottom	RIA/Vacutainer®/Sarstedt®	Round Bottom	Conical Bottom
Tube Volume	50 ml	1.5/2.0 ml	7 ml	5 ml	15 ml	
Tubes per Rotor	10					
Max. Tube Diameter (mm)	29	11	13		17	
Tube Height (mm)	118	42	95/115	65/75	97/123	120

*Only possible with adapter 30472300 or 30472307



Angle Rotor 30 x 15 ml	
Item No.	30314832
Rotor Capacity	30 x 15 ml
Rotor Type	Angle, 35°
Permissible Net Weight	30 x 32 g
Lowest Temperatures	-7 °C

Accessory Specifications	n/a				
Accessory Item No.	n/a	30211180	30130886	30130889	30130890
Accessory Type	n/a	Adapter			
Max. RPM (FC5718/FC5718R)	4,500				
Quantity in Package	n/a	2/pk	6/pk	2/pk	
Max. RCF (FC5718/FC5718R)	2,830 x g	2,716 x g / 2,354 x g	2,038 x g	2,762 x g	2,377 x g
Tube Specifications					
Tube Type	Round Bottom/Conical Bottom	Vacutainer® / Sarstedt®	Microtube	Round Bottom/Vacutainer®	RIA/Vacutainer®/Sarstedt®
Tube Volume	15 ml	9-10ml	1.5/2.0 ml	7 ml	5 ml
Tubes per Rotor	30	20	30	20	
Max. Tube Diameter (mm)	17	16	11	13	
Tube Height (mm)	95/120	92-107	42	95/115	65/75