










Rotors for FRONTIER™ FC5916 and FC5916R




Angle Rotor 6 × 50 ml	
Item No.	30314831
Rotor Capacity	6 x 50 ml
Rotor Type	Angle, 26°
Permissible Net Weight	6 x 94 g
Lowest Temperatures	-9 °C

Accessory Specifications	n/a				
Accessory Item No.	n/a	30130891	30130892	30130893	30314892*
Accessory Type	n/a	Adapter			
Max. RPM (FC5916/FC5916R)	13,000				
Quantity in Package	n/a	2/pk			
Max. RCF	15,869 × g	14,649 × g	13,777 × g	13,951 × g	13,428 × g
Tube Specifications					
Tube Type	Round Bottom Oakridge	Round Bottom			Conical Bottom
Tube Volume	50 ml	30 ml	16 ml	15 ml	
Tubes per Rotor	6				
Max. Tube Diameter (mm)	29	25	18	17	
Tube Height (mm)	95/115	92/95	100/105		120

*Only without rotor lid



Angle Rotor 20 × 10 ml	
Item No.	30314833
Rotor Capacity	20 x 10 ml
Rotor Type	Angle, 30°
Permissible Net Weight	20 x 18 g
Lowest Temperatures	-7 °C

Accessory Specifications	n/a
Accessory Item No.	n/a
Accessory Type	n/a
Max. RPM (FC5916/FC5916R)	12,000
Quantity in Package	n/a
Max. RCF	15,775 × g
Tube Specifications	
Tube Type	Round Bottom
Tube volume	10 ml
Tubes per Rotor	20
Max. Tube Diameter (mm)	16
Tube Height (mm)	80

*No Adapters

Rotors for FRONTIER™ FC5830R



Angle Rotor 6 x 50 ml	
Item No.	30314831
Rotor Capacity	6 x 50 ml
Rotor Type	Angle, 26°
Permissible Net Weight	6 x 94 g
Lowest Temperatures	10 °C

Accessory Specifications	n/a				
Accessory Item No.	n/a	30130891	30130892	30130893	30314892*
Accessory Type	n/a	Adapter			
Max. RPM	21,000				
Quantity in Package	n/a	2/pk			
Max. RCF	41,410 x g	40,242 x g	38,945 x g	39,438 x g	37,959 x g
Tube Specifications					
Tube Type	Round Bottom Oakridge	Round Bottom			Conical Bottom
Tube Volume	50 ml	30 ml	16 ml	15 ml	
Tubes per Rotor	6				
Max. Tube Diameter (mm)	29	25	18	17	
Tube Height (mm)	95/115	92/95	100/105		120

*Only without bucket lid



Angle Rotor 20 x 10 ml	
Item No.	30314833
Rotor Capacity	20 x 10 ml
Rotor Type	Angle, 30°
Permissible Net Weight	20 x 18 g
Lowest Temperatures	6 °C


Accessory Specifications	n/a
Accessory Item No.	n/a
Accessory Type	n/a
Max. RPM	16,000
Quantity in Package	n/a
Max. RCF	28,045 x g
Tube Specifications	
Tube Type	Round Bottom
Tube volume	10 ml
Tubes per Rotor	20
Max. Tube Diameter (mm)	16
Tube Height (mm)	80

*No Adapters

Rotors for FRONTIER™ FC5816 and FC5816R








Angle Rotor 20 x 10 ml	
Item No.	30314833
Rotor Capacity	20 x 10 ml
Rotor Type	Angle, 30°
Permissible Net Weight	20 x 18 g
Lowest Temperatures	0 °C

Accessory Specifications	n/a
Accessory Item No.	n/a
Accessory Type	n/a
Max. RPM (FC5816/FC5816R)	12,000
Quantity in Package	n/a
Max. RCF (FC5816/FC5816R)	15,775 x g
Tube Specifications	
Tube Type	Round Bottom
Tube volume	10 ml
Tubes per Rotor	20
Max. Tube Diameter (mm)	16
Tube Height (mm)	80

*No Adapters




Angle Rotor 44 x 1.5/2.0 ml	
Item No.	30372718
Rotor Capacity	44 x 1.5/2.0 ml
Rotor Type	Angle, 30°/55°
Permissible Net Weight	44 x 3.4 g
Lowest Temperatures	4 °C

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM (FC5816/FC5816R)		15,000/16,000	
Quantity in Package	n/a	6/pk	
Max. RCF (FC5816/FC5816R)	21,379/24,325 x g	20,625/23,466 x g	18,864/21,463 x g
Tube Specifications			
Tube Type		Microtube	
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor		44	
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	

Rotors for FRONTIER™ FC5720R










Angle Rotor 20 x 10 ml	
Item No.	30314833
Rotor Capacity	20 x 10 ml
Rotor Type	Angle, 30°
Permissible Net Weight	20 x 18 g
Lowest Temperatures	-1 °C

Accessory Specifications	n/a
Accessory Item No.	n/a
Accessory Type	n/a
Max. RPM	14,000
Quantity in Package	n/a
Max. RCF	21,472 x g
Tube Specifications	
Tube Type	Round Bottom
Tube volume	10 ml
Tubes per Rotor	20
Max. Tube Diameter (mm)	16
Tube Height (mm)	80


*No Adapters
















Angle Rotor 12 x 15 ml	
Item No.	30314834
Rotor Capacity	12 x 15 ml
Rotor Type	Angle, 32°
Permissible Net Weight	12 x 25 g
Lowest Temperatures	-20 °C


Accessory Specifications	n/a			
Accessory Item No.	n/a	30130886	30130889	30130890
Accessory Type	n/a	Adapter		
Max. RPM	6,000			
Quantity in Package	n/a	6/pk	2/pk	
Max. RCF	4,427 x g	3,059 x g	4,266 x g	3,662 x g
Tube Specifications				
Tube Type	Round Bottom / Conical Bottom	Microtube	Round Bottom/Vacutainer®	Round Bottom
Tube Volume	15 ml	1.5/2.0 ml	7 ml	5 ml
Tubes per Rotor	12			
Max. Tube Diameter (mm)	17	11	13	
Tube Height (mm)	120	42	95/115	65/90


Rotors for FRONTIER™ FC5718 and FC5718R

	Angle Rotor 6 × 50 ml	
	Item No.	30314830
	Rotor Capacity	6 x 50 ml
	Rotor Type	Angle, 40°
	Permissible Net Weight	6 x 72 g
	Lowest Temperatures	-6 °C

Accessory Specifications	n/a							
Accessory Item No.	n/a	30130886*	30130889*	30130890*	30130891	30130892	30130894	
Accessory Type	n/a	Adapter						
Max. RPM (FC5718/FC5718R)	6,000							
Quantity in Package	n/a	6/pk	2/pk					
Max. RCF (FC5718/FC5718R)	4,427 x g	2,696 x g	4,105 x g	3,340 x g	4,306 x g	4,145 x g	4,266 x g	
Tube Specifications								
Tube Type	Round Bottom	Conical Bottom	Microtube	Round Bottom	RIA/ Vacutainer®/ Sarstedt®	Round Bottom		Round Bottom/ Conical Bottom
Tube volume	50 ml		1.5/2.0 ml	7 ml	5 ml	30 ml	16 ml	15 ml
Tubes per Rotor	6							
Max. Tube Diameter (mm)	29		11	13		26	17	18
Tube Height (mm)	100/120	116	42	95/100	65/75	100	100/105	120

*Only possible with adapter 30130894

	Angle Rotor 20 × 10 ml	
	Item No.	30314833
	Rotor Capacity	20 x 10 ml
	Rotor Type	Angle, 30°
	Permissible Net Weight	20 x 18 g
	Lowest Temperatures	4 °C

Accessory Specifications	n/a
Accessory Item No.	n/a
Accessory Type	n/a
Max. RPM (FC5718/FC5718R)	12,000
Quantity in Package	n/a
Max. RCF (FC5718/FC5718R)	15,775 x g
Tube Specifications	
Tube Type	Round Bottom
Tube volume	10 ml
Tubes per Rotor	20
Max. Tube Diameter (mm)	16
Tube Height (mm)	80

*No Adapters