













Rotors for FRONTIER™ FC5916 and FC5916R

	Angle Rotor 44 × 1.5/2.0 ml	
	Item No.	30372718
	Rotor Capacity	44 x 1.5/2.0 ml
	Rotor Type	Angle, 32°/55°
	Permissible Net Weight	44 x 3.4 g
Lowest Temperatures	-3 °C	

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM (FC5916/FC5916R)	16,000/16,000		
Quantity in Package	n/a	6/pk	
Max. RCF	24,325/24,325 × g	23,466/23,466 × g	21,463/21,463 × g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	44		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	

	Angle Rotor 30 × 1.5/2.0 ml Sealable	
	Item No.	30314836
	Rotor Capacity	30 x 1.5/2.0 ml
	Rotor Type	Angle, 45°
	Permissible Net Weight	30 x 3.4 g
Lowest Temperature	-3 °C	






Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM (FC5916/FC5916R)	15,000/15,000		
Quantity in Package	n/a	6/pk	
Max. RCF	23,643/23,643 × g	21,361/21,361 × g	19,719/19,719 × g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	30		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	20	30

*No Adapters

Rotors for FRONTIER™ FC5830R










Angle Rotor 30 × 1.5/2.0 ml Sealable	
Item No.	30314836
Rotor Capacity	30 × 1.5/2.0 ml
Rotor Type	Angle, 45°
Permissible Net Weight	30 × 3.4 g
Lowest Temperature	8 °C

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM	30,000		
Quantity in Package	n/a	6/pk	
Max. RCF	42,032 x g	40,690 x g	37,560 x g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	30		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	








Angle Rotor 12 × 1.5/2.0 ml	
Item No.	30314839
Rotor Capacity	12 × 1.5/2.0 ml
Rotor Type	Angle, 40°
Permissible Net Weight	12 × 3.4 g
Lowest Temperatures	6 °C

Accessory Specifications	n/a			
Accessory Item No.	n/a	30314900	30130885	30130884
Accessory Type	n/a	Adapter		
Max. RPM	30,000			
Quantity in Package	n/a	6/pk		
Max. RCF	65,395 x g	64,389 x g	56,340 x g	63,383 x g
Tube Specifications				
Tube Type	Microtube			
Tube Volume	1.5/2.0 ml	1.5 ml	0.5 ml	0.2/0.4 ml
Tubes per Rotor	12			
Max. Tube Diameter (mm)	11	11	8	6
Tube Height (mm)	40	42	45	

Rotors for FRONTIER™ FC5720R








Angle Rotor 44 × 1.5/2.0 ml	
Item No.	30372718
Rotor Capacity	44 x 1.5/2.0 ml
Rotor Type	Angle, 32°/55°
Permissible Net Weight	44 x 3.4 g
Lowest Temperatures	-6 °C

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM	15,000		
Quantity in Package	n/a	6/pk	
Max. RCF	21,379 x g	20,625 x g	18,864 x g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	44		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	



Angle Rotor 30 × 1.5/2.0 ml Sealable	
Item No.	30314836
Rotor Capacity	30 x 1.5/2.0 ml
Rotor Type	Angle, 45°
Permissible Net Weight	30 x 3.4 g
Lowest Temperature	7 °C

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM	17,000		
Quantity in Package	n/a	6/pk	
Max. RCF	30,368 x g	29,399 x g	27,137 x g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	30		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	

Rotors for FRONTIER™ FC5718 and FC5718R



Angle Rotor 12 × 5 ml FA Sealable	
Item No.	83041010
Rotor Capacity	12 × 5 ml
Rotor Type	Angle, 45°
Permissible Net Weight	12 × 9.5 g
Lowest Temperature	2 °C

Accessory Specifications	n/a			
Accessory Item No.	n/a	30130886	30130887	30130888
Accessory Type	n/a	Adapter		
Max. RPM (FC5718/FC5718R)	4,500	14,000/15,000		
Quantity in Package	n/a	6/pk		
Max. RCF (FC5718/FC5718R)	18,624/21,379 x g	15,337/17,606 x g	15,994/18,361 x g	16,433/18,864 x g
Tube Specifications				
Tube Type	Microtube		Cryo Tube - Flat Bottom	Cryo Tube - Round Bottom
Tube Volume	5 ml	1.5/2.0 ml	1.0 ml	1.8 ml
Tubes per Rotor	12			
Max. Tube Diameter (mm)	17	11	12.6	
Tube Height (mm)	60	42	41	48



Angle Rotor 30 × 1.5/2.0 ml Sealable	
Item No.	30314836
Rotor Capacity	30 × 1.5/2.0 ml
Rotor Type	Angle, 45°
Permissible Net Weight	30 × 3.4 g
Lowest Temperatures	6 °C

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM (FC5718/FC5718R)	13,000/14,000		
Quantity in Package	n/a	6/pk	
Max. RCF (FC5718/FC5718R)	17,758/20,595 x g	17,191/19,937 x g	15,869/18,404 x g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	30		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	

Rotors for FRONTIER™ FC5714



Angle Rotor 12 x 15 ml	
Item No.	30314834
Rotor Capacity	12 x 15 ml
Rotor Type	Angle, 32°
Permissible Net Weight	12 x 25 g
Lowest Temperature	n/a

Accessory Specifications	n/a			
Accessory Item No.	n/a	30130886	30130889	30130890
Accessory Type	n/a	Adapter		
Max. RPM	6,000			
Quantity in Package	n/a	6/pk	2/pk	
Max. RCF	4,427 x g	3,059 x g	4,266 x g	3,662 x g
Tube Specifications				
Tube Type	Round Bottom / Conical Bottom	Microtube	Round Bottom/Vacutainer®	Round Bottom
Tube Volume	15 ml	1.5/2.0 ml	7 ml	5 ml
Tubes per Rotor	12			
Max. Tube Diameter (mm)	17	11	13	
Tube Height (mm)	120	42	95/115	65/90



Angle Rotor 30 x 1.5/2.0 ml Sealable	
Item No.	30314836
Rotor Capacity	30 x 1.5/2.0 ml
Rotor Type	Angle, 45°
Permissible Net Weight	30 x 3.4 g
Lowest Temperature	n/a

Accessory Specifications	n/a		
Accessory Item No.	n/a	30130884	30130885
Accessory Type	n/a	Adapter	
Max. RPM	12,000		
Quantity in Package	n/a	6/pk	
Max. RCF	15,131 x g	13,521 x g	14,648 x g
Tube Specifications			
Tube Type	Microtube		
Tube volume	1.5/2.0 ml	0.2/0.4 ml	0.5 ml
Tubes per Rotor	30		
Max. Tube Diameter (mm)	11	6	8
Tube Height (mm)	40	45	