

Problem	Possible Causes	Corrective Action
Fault code 11 on display	Internal probe failure	Contact supplier
Fault code 05 on display	Interference on electrical power line Triac failure	Check and correct as required. Contact supplier.

Technical Information

Performance Specifications

Operating Temperature:	Fixed at 4°C (other factory-set operating temperatures available)
Temperature Stability:	±0.1°C
Temperature Units:	°C
Reservoir Capacity:	13.8 gallons / 52.24 liters
Compressor:	¼ HP
Working Access:	20.6 x 13 x 12" / 52.4 x 33 x 30.5 cm (L x W x D)
Overall Dimensions:	28 x 14.5 x 36.6" / 71.1 x 37 x 93 cm (L x W x H)
Shipping Weight:	200 lbs / 90.6 kg
Electrical Requirements:	120V, 60Hz, 11.25A 240V, 50Hz, 9.0A

Specifications subject to change without notice

Environmental Conditions

Indoor use only
Maximum Altitude: 2000 meters
Operating Ambient: 5° to 35°C
Relative Humidity: 80% for temperatures to 35°C
Pollution Degree: 2
Class 1: Residential, Commercial, Light Industrial
Class 2: Heavy Industrial