

Specifications	SCI500HS-Pro	SCI550-Pro	SCI550-S
Work plate Dimension [W x D]	254x254mm (10 inch)	184x184mm (7 inch)	184x184mm (7 inch)
Work plate material	Glass ceramic	Glass ceramic	Glass ceramic
Motor type	Brushless DC motor	Brushless DC motor	Shaded pole motor
Stirring positions	1	1	1
Max. stirring quantity, [HzO]	30L	20L	10L
Max. magnetic bar[length]	80mm	80mm	80mm
Speed range	100–1500rpm, resolution ± 1 rpm	100–1500rpm, resolution ± 1 rpm	0–1500rpm
Speed display	–	LCD	Scale
Temperature display	LCD	LCD	LED
Heating temperature range	Room Temp.–500°C, increment 1°C	Room Temp.–550°C, increment 1°C	Room Temp.–550°C, increment 5°C
Temperature control accuracy	$\pm 1^\circ\text{C}(<100^\circ\text{C}) \pm 1\%(>100^\circ\text{C})$	$\pm 1^\circ\text{C}(<100^\circ\text{C}) \pm 1\%(>100^\circ\text{C})$	$\pm 10^\circ\text{C}$
Overheating protection	540°C	580°C	580°C
Temperature display accuracy	$\pm 0.1^\circ\text{C}$	$\pm 0.1^\circ\text{C}$	$\pm 1^\circ\text{C}$
External temperature sensor	PT1000(accuracy $\pm 0.2^\circ\text{C}$)	PT1000(accuracy $\pm 0.2^\circ\text{C}$)	PT1000(accuracy $\pm 0.2^\circ\text{C}$)
"Hot" warning	50°C	50°C	50°C
Data connector	SD card	RS232	–
Protection class	IP21	IP21	IP21
Motor rating input	–	18W	15W
Motor rating output	–	10W	1.5W
Power	1400W	1050W	1030W
Heating output	1350W	1000W	1000W
Voltage	100–120/200–240V, 50/60Hz	100–120/200–240V, 50/60Hz	100–120/200–240V, 50/60Hz
Dimension [WxDxH]	328x424x138mm	215x360x112mm	215x360x112mm
Weight	7.18kg	5.3kg	4.5kg
Timer function	1min–99h59min	–	–
Permissible ambient temperature and humidity	5–40°C,80%RH	5–40°C,80%RH	5–40°C,80%RH



Overheating protection



External sensor



Chemical resistance



Wide range of accessories