

Orbital Shaking from 35-300RPM with Temperature Control

Interchangeable Platforms

 <p>300 RPM with Ultra High Torque</p>	 <p>Unique Temperature Flow</p>	 <p>Durable No-walk Housing</p>	 <p>28° to 75° C</p>
--	--	--	---

Access samples 3 ways - Door, Kickstand (back, left, or right) or Removable Cover



Universal Ratcheting Clamps

Provides the flexibility for using a mix of different size and shape vessels or large volume on a single platform.



Standard Flask Clamps

Equipped with a platform to accept various size flasks or beakers.

Clamps sold separately.



Adhering Mat

Provides a flat platform with adhering rubber mat perfect for use with open containers. Patented material is naturally adhering. Rinse clean to renew adhering properties.

Specifications

Speed (RPM)	35-300 RPM
Orbit	19mm
Temperature	28° to 75° C
Weight	9 Kg (20 lbs.)
Dimensions	450 x 480mm (17.6 x 19in)
Platform	305 x 305 mm (12 x 12in)
Platform Weight Capacity	3 Kg (6.6 lbs)
Chamber Height	305mm (12in)
Chamber Volume	40 L (2400 cubic inches)

Ordering Information

Voltage & Plug configuration	GTS 300 Ratcheting Clamps	GTS 300 Flask Clamps	GTS 300 Adhering Mat
120V - U.S Standard	SI-G1500	SI-G1600	SI-G1700
230V - No Plug	SI-G1501	SI-G1601	SI-G1701
230V - European Plug	SI-G1502	SI-G1602	SI-G1702
230V - British Plug	SI-G1503	SI-G1603	SI-G1703
230V - Swiss Plug	SI-G1504	SI-G1604	SI-G1704
240V - Aust. Plug	SI-G1506	SI-G1606	SI-G1706
100V	SI-G1505	SI-G1605	SI-G1705

Accessory Ordering Information

Catalog No.	Description	Platform Capacity *
SI-1610	100 mL Flask Clamp	16
SI-1611	125/150 mL Flask Clamp	16
SI-1612	250 mL Flask Clamp	16
SI-1613	500 mL Flask Clamp	9
SI-1614	1 L Flask Clamp	5
SI-1615	2 L Flask Clamp	3

* See platform weight capacity

Catalog No.	Description
SI-1616	Double Sided Adhesive Tape, 60inx 1in (1.5m x 25.5mm)
SI-M1617	Adhering Mat, Blue, 300mm x 300mm (11.8in x 11.8in)
SI-G150	GTS Non-Slip Platform (for low speed)
SI-M150	Stacking Tray (requires GTS Non-Slip Platform)
SI-G1550	GTS Ratcheting Clamp Platform
SI-G1650	GTS Flask Clamp Platform
SI-G1750	GTS Adhering Mat Platform

