

SCI-Vac-E

Economical Vacuum Aspirator

Small, compact and easy to use system for the convenient handling of liquid waste disposal.

Easy to switch between manual aspiration and two-level adjustable continuous aspiration:
 Level 1: Standard continuous aspiration mode.
 Level 2: Fast continuous aspiration mode enhanced



Hanging handles on both sides

Vacuum level indicator light

Features

- Small and compact to fit in the cabinet, on the benchtop or even beneath the bench
- Easy to switch between manual aspiration and continuous aspiration mode, reducing RSI (Repetitive Strain Injury) and improving efficiency
- Collection bottle outlet with hydrophobic filter prevents aerosol and liquid contamination
- Brushless motor offers low noise and long life
- Different adapters are available to fit a multitude of laboratory supplies
- The parts in contact with liquids can be autoclaved
- Adjustable vacuum level with indicator light is designed for various applications

Specifications

Vacuum range	0–500mbar
Aspirating speed	15L/min(air)
Flow rate [liquid]	17mL/s
Bottle	2L standard, 1L optional with adaptor
Motor type	Brushless Motor
Input voltage	100–220VAC, 50/60Hz
Dimension [W×D×H]	180×240×340 mm
Weight	2.8kg