

9. Specification

Items	Specifications	
	Analog Model	LED Digital Model
Voltage [VAC]	100-240	100-240
Frequency [Hz]	50/60	50/60
Motor rating input[W]	16	16
Motor rating output[W]	10	10
Shaking motion	Rocking/3D	Rocking/3D
Tile Angel [°]	±7°	±7°
Max. load capacity (with platform) [Kg]	3	3
Motor type	DC motor	DC motor
Speed range[rpm]	0-80	10-80
Dimensions[W×H×D mm]	330×270×120	330×270×120

Items	Specifications	
	Analog Model	LED Digital Model
Operation type	Continuous	Continuous/time d
Time setting range	-	1min-19h59min
Weight[kg]	2.7	2.7
Permissible ambient temperature[°C]	5-40	5-40
Permissible relative humidity	80%	80%
Protection class acc. DIN EN60529	IP21	IP21