

SECTION 06 | SPECIFICATIONS



STORM5000

Air Flow Rate (lpm)	CFM (L/min) @ 60 Hz 1.3 (37) CFM (L/min) @ 50 Hz 1.1 (31)
Maximum Vacuum, Hg	24"
Ultimate Pressure, Torr (mbar)	150 (200)
Tubing Needed, I.D.	1/4"
Cord Supplies	North American 115V Plug or North American 230V and 230V European Shuko
Motor H.P.	1/5
Usage Hours	15,000
Motor Voltage & Frequency	115V, 60Hz, 1 Phase
Motor Amps	3.5
Overall Pump Dimensions	8.75"L x 5.0"W x 8.75"H
Shipping Dimensions	20" L x 16"W x 14"H
Weight	13 lbs.
Shipping Weight	16 lbs.
Certification	UL Recognized
Warranty	One Year Warranty



STORM3000

Air Flow Rate (lpm)	CFM (L/min) @ 60 Hz 0.7 (20)
Maximum Vacuum, Hg	22"
Ultimate Pressure, Torr (mbar)	190 (253)
Tubing Needed, I.D.	1/4"
Cord Supplies	North American 115V Plug
Motor H.P.	1/7
Usage Hours	15,000
Motor Voltage & Frequency	115V, 60Hz, 1 Phase
Motor Amps	1.5
Overall Pump Dimensions	6.8"L x 7.3"W x 8.3"H
Shipping Dimensions	14"L x 14"W x 14"H
Weight	7.5 lbs.
Shipping Weight	10 lbs.
Certification	UL Recognized
Warranty	One Year Warranty