

## 120 V, 60 Hz

Centrifuge	Sorvall Legend Micro 17	Sorvall Legend Micro 21
Catalog Number	75002431	75002436
Places / Volume	24 x 1.5 / 2 ml	24 x 1.5 / 2 ml
Maximum permissible Load [ g ]	24 x 4	24 x 4
Maximum Speed $n_{\max}$ [ rpm ]	13300	14800
Maximum RCF-Value at $n_{\max}$	17000	21100
Radius max. / min. [ cm ]	8.6 / 5.1	8.6 / 5.1
Angle [ ° ]	45	45
Acceleration / Braking Time [ s ]	11 / 12	13 / 13
Sample Heating at $n_{\max}$ [ °C ] referred to Ambient Temperature of 23 °C, Running Time 60 Minutes	33	36
Aerosol-tight*	yes	yes
Permissible Temperature Range autoclavable (Number of Cycles)	121 °C (20 Cycles)	121 °C (20 Cycles)

\*Tested and approved by HPA, Porton-Down, UK

Centrifuge	Sorvall Legend Micro 17R	Sorvall Legend Micro 21R
Catalog Number	75002441	75002446
Places / Volume	24 x 1.5 / 2 ml	24 x 1.5 / 2 ml
Maximum permissible Load [ g ]	24 x 4	24 x 4
Maximum Speed $n_{\max}$ [ rpm ]	13300	14800
Maximum RCF-Value at $n_{\max}$	17000	21100
Radius max. / min. [ cm ]	8.6 / 5.1	8.6 / 5.1
Angle [ ° ]	45	45
Acceleration / Braking Time [ s ]	10 / 12	12 / 13
Min. Temperature at $n_{\max}$ [ °C ] referred to Ambient Temperature of 23 °C	≤0	≤0
Aerosol-tight*	yes	yes
Permissible Temperature Range autoclavable (Number of Cycles)	121 °C (20 Cycles)	121 °C (20 Cycles)

\*Tested and approved by HPA, Porton-Down, UK