

Model	Chamber Volume	Standard Cassettes Capacity	No. of Trays	Tray Dimensions WxHxD (mm)	Voltage(V) Frequency (Hz)	Current(A) Power(W)	Overall Dimensions WxHxD (mm)	Autoclave Weight (kg)
-------	----------------	-----------------------------	--------------	----------------------------	---------------------------	---------------------	-------------------------------	-----------------------

**EA Series**

<b>3850EA</b>	65 Liter	10 full	2	495x25x286 495x25x350	230V (50/60 Hz)	10.4A 2400W	660x525x695	70
<b>3870EA</b>	85 Liter	15 full	2	675x25x286 675x25x350	230V (50/60 Hz)	13A 3000W	660x525x875	81

**EKA Series**

<b>2540EKA</b>	23 Liter	3 full/3 half	4	168x20x414	230V (50/60 Hz)	9.6A 2200W	508x362x550	37
----------------	----------	---------------	---	------------	--------------------	------------	-------------	----

**M Series**

<b>2340M</b>	19 Liter	2 full/2 half	3	168x20x414	120/230V (50/60 Hz)	11.7/6A 1400W	508x362x550	30
<b>2540M</b>	23 Liter	3 full/3 half	4	168x20x414	120/230V (50/60 Hz)	11.7/6A 1400W	508x362x550	33
<b>3850M</b>	65 Liter	10 full	2	495x25x286 495x25x350	230V (50/60 Hz)	10.4A 2400W	660x525x695	69
<b>3870M</b>	85 Liter	15 full	2	675x25x286 675x25x350	230V (50/60 Hz)	13A 3000W	660x525x875	78

**MK Series**

<b>1730MK</b>	7.5 Liter	2 half	3	115x20x290	120/230V (50/60 Hz)	11.3/5.9A 1350W	442x307x460	20
<b>2340MK</b>	19 Liter	2 full/2 half	3	168x20x414	230V (50/60 Hz)	9.6A 2200W	508x362x550	31
<b>2540 MK</b>	23 Liter	3 full/3 half	4	168x20x414	230V (50/60 Hz)	9.6A 2200W	508x362x550	33

