

Magnetic Stirrer

Suitable for stirring heating baths

MB800-115V / MB800-220V

Stirring rate 70 ~ 1200 rpm

Stirring capacity 100 ml to 10L



Equipped with optimum heat prevention function for oil bath

- Chemical-proof, anodized aluminum finish top plate
- Employs a magnetic stirrer bar to agitate solutions
- High-powered electronic controlled AC motor which provides stable rotation
- Power supply to the outlet for oil bath can be cut off and stopped when the temperature of the bottom of the oil bath reaches the specified value
- Suitable for BO500 oil bath

Specifications

Model	MB800-115V	MB800-220V
Top plate material	Aluminum	
Top plate dimensions	W250×D270 mm	
Stirring capacity	100 ~ 10000 ml	
Stirring rate	70 ~ 1200 rpm	
Temp. control	Triac input control type	
Motor	AC motor, condenser motor	
Overheat prevention function	70 to 200°C	
Sensor	Thermistor type	
Safety device	Overheat prevention device for oil bath, earth leakage breaker	
Power source (50/60Hz)	AC115V 8.7A with external transformer	AC220V 4.5A with external transformer
External dimensions*	W250 × D270 × H150 mm	
Weight	~4.2kg	
Included accessory	Magnetic stirrer bar 40mm 1pc.	

* Protrusions excluded