

nEXT730, 930 AND 1230 TURBOMOLECULAR PUMP

edwardsvacuum.com

Edwards are proud to offer the nEXT730, nEXT930 and nEXT1230 turbomolecular pumps, these larger pumps offer choices for customers requiring higher pumping speeds from 730 up to 1250 l/s for nitrogen.

As well as addressing the general R&D market, where faster pumping speeds are sometimes required, these pumps are also designed to meet the requirements of the coating market and other diffuse market sectors such as Heat treatment, Furnace applications, Ebeam welding, Etch, Ion implant, Degassing and Cylinder evacuation.

For our OEM customers derivative versions of these products can be developed, just like the existing nEXT pumps, and like the existing nEXT pumps split flow variants are possible. This will give benefits for our customers with larger instruments as well as the possibility to reduce the total number of pumps on existing instruments.

The new products offer market leading performance for pumps of their class, and in a compact footprint. The pumps feature bearings with a typical life time of at least 4 years with no maintenance, which can then be replaced simply and economically by the customer themselves when required or customers may choose from our other service support offerings.

The pumps are able to operate in any orientation, and are supported by a full range of accessories for cooling, venting, powering and control.

FEATURES AND BENEFITS

- Class leading pumping speeds
- Outstanding compression ratios
- Ease of integration and installation
- Assured reliability
- End user service capability
- Full nEXT established communication interface





FECHNICAL DATA		nEXT730D		nEXT930D		nEXT1230H		
Inlet flange		DN 160 ISO-K	DN 160 CF	DN 200 ISO-K	DN 200 CF	DN 200 CF	DN 200 ISO-F	DN 200 ISO-
Main inlet pumping speed								
	N ₂	730		925		1250		
Inlet pumping speed Is ⁻¹	Ar	665		865		1150		
	He	820		905		1350		
	H ₂	715		735		1150		
Gas throughput								
	N ₂	14 12						
Gas throughput mbar Is-1	Ar	3.5			4			
	He	21				>20		
	H ₂	>> 14			>20			
Peak compression ratio backing port t	to main inlet	port						
Compression ratio	N ₂	> 1x10¹¹						
	Ar	> 1x10 ¹¹						
	He	1,2x10 ⁸				4x10 ⁺⁸		
	H ₂	4,0x10 ⁶			1x10 ⁺⁷			
Ulimate pressure with 2-stage oil sealed rotary vane pump ISO-K/CF	mbar	< 3,5x10 ⁻⁹ < 6x10 ⁻¹⁰ < 3,5x10 ⁻⁹ < 6x10 ⁻¹⁰			<5x10 ⁻¹⁰ indicate higher pressure for ISO-K and ISO-F			
Backing/interstage/boost ports	mbar				15	ļ.		
Normal rotational speed	rpm	49 200			42 000			
Start time to 90% speed (sec) D/H (T)	min	2.5			3			
Max. power consumption	W	500 (default), 600 (max.)			660 (default), 800 (max.)			
Power consumption at ultimate pressure	W	40			50			
Type of protection	IP	54						
Recommended cooling method		Water*						
Optional cooling		Forced air cooling*						
Cooling water connection		Plug-in connection for 6x1 hose/alternative G 1/8"						
Cooling water consumption	l/h	60						
Critical backing pressure	mbar	15						
Permissible cooling water temperature	°C	15 to 35						
Mass (kg) D/H (T)	kg	14.6	19.6	15.4	21.7	32.6	24.9	23.7
Recommended backing pump*		nXRi, XDS35i, E2N		128**				
Noise level with convection cooling with radial air cooler	dB(A)	< 40 < 55	< 40 < 55	< 40 < 55	< 40 < 55	< 44 < 55	< 44 < 55	< 44 < 55
Water cooled/forced air cooled max. bake out	°C	100 n/a 100 n/a						
Purge gas flow	mbar · Is ⁻¹ sccm	0.4 24						
Vent/purge port		G 1/8"						

^{*}Depending on the ambient temperature, the gas type and throughput, performance may be limited by the cooling method.
**Please contact your local representative to discuss the correct option for your application.

Publication Number: 3601 0621 01 Issue 2 © Edwards Limited 2021. All rights reserved. Edwards and the Edwards logo are trademarks of Edwards Limited.

Whilst we make every effort to ensure that we accurately describe our products and services, we give no guarantee as to the accuracy or completeness of any information provided in this datasheet.

Edwards Ltd, registered in England and Wales No. 6124750, registered office: Innovation Drive, Burgess Hill, West Sussex, RH15 9TW, UK.

GLOBAL CONTACTS

EMEA		ASIA PACIFIC	
UK	0345 9 212 223 +44 1444 253 000	China India	+86 400 111 9618 +91 20 4075 2222
Belgium France	+44 1293 60 3350 +33 1 4121 1256	Japan Korea	+81 47 458 8836 +82 31 716 7070
Germany	0800 000 1456	Singapore	+65 6546 8408
Italy Israel	+39 02 48 4471 +972 8 681 0633	Taiwan	+886 3758 1000
Russia	+7 495 933 55 50 Ext. 1800/1803	AMERICAS	
	+8 800 775 80 99	USA	+1 800 848 9800
		Brazil	+55 11 3952 5000

